

Technical Advisory Service
e-mail: rawlinfo@bpb.com OR rawltech@bpb.com

Product Information



Typical applications

Tough and versatile drill bit for a variety of masonry substrates including brick, concrete, hard stone, lightweight block, ceramic tiles etc.

DESCRIPTION

All-purpose masonry drill bit for rotary percussive drilling machines.

Features

1. Brass brazed tungsten carbide tip, for high drilling speeds.

Blue Flash™

Product Information



Typical applications

The professional's choice for concrete, engineering brick, lightweight block and ceramic tiles.

Heavy-duty professional's masonry drill bit for use with rotary hammer action drills.

DESCRIPTION

Masonry bit for mains and cordless drilling machines. Drills more holes per battery charge than other masonry bits.

Sizes and lengths of up to 400mm. Extension bars available for deeper drilling. Packed in re-sealable tubes.

Features

1. High grade alloy tool steel and furnace hardened to SDS standards, making bits stronger, more durable and safer to use.
2. Geometrically designed flute maximises spoil evacuation.
3. Copper brazed carbide tip, strengthens the bond between tip & body.

Impactor®

Diameter	Length	Product code	Quantity
4	75	31-008	Box of 10
4.5	85	31-009	Box of 10
4.5	150	31-109	Box of 10
5	85	31-010	Box of 10
5	150	31-110	Box of 10
5.5	85	31-011	Box of 10
5.5	150	31-111	Box of 10
6	100	31-012	Box of 10
6	150	31-112	Box of 10
6	200	31-212	Box of 10
6.5	100	31-013	Box of 10
6.5	150	31-113	Box of 10
7	100	31-014	Box of 10
7	150	31-114	Box of 10
8	120	31-016	Box of 10
8	150	31-116	Box of 10
8	200	31-216	Box of 10
10	120	31-020	Box of 10
10	150	31-120	Box of 10
10	200	31-220	Box of 10
10	400	31-420	Single
12	150	31-124	Box of 10
12	200	31-224	Box of 10
12	400	31-424	Single
13	150	31-126	Box of 10
14	150	31-128	Single
14	400	31-426	Single
16	150	31-132	Single
16	400	31-432	Single
20	150	31-140	Single
20	400	31-440	Single
22	400	31-444	Single
25	400	31-450	Single

PRODUCT DESCRIPTION	EFFECTIVE LENGTH	PRODUCT CODE	QUANTITY
EXTENSION SLEEVE 14-16MM	250	82-032	Tube of 1
EXTENSION SLEEVE 20-25MM	250	83-050	Tube of 1

Diameter	Length	Product code	Quantity
4.5	85	32-009	Tube of 1x10
5	100	32-010	Tube of 1x10
5	150	32-110	Tube of 1
5.5	100	32-011	Tube of 1x10
5.5	150	32-111	Tube of 1
6	100	32-012	Tube of 1x10
6	150	32-112	Tube of 1
6.5	100	32-013	Tube of 1x10
6.5	150	32-113	Tube of 1
7	100	32-014	Tube of 1x10
7	150	32-114	Tube of 1
7	300	32-314	Tube of 1
8	120	32-016	Tube of 1x10
8	150	32-116	Tube of 1
8	200	32-216	Tube of 1
8	300	32-316	Tube of 1
10	120	32-020	Tube of 1x10
10	150	32-120	Tube of 1
10	200	32-220	Tube of 1
10	300	32-320	Tube of 1
10	400	32-420	Tube of 1
12	150	32-124	Tube of 1
12	200	32-224	Tube of 1
12	300	32-324	Tube of 1
12	400	32-424	Tube of 1
13	150	32-126	Tube of 1
13	400	32-426	Tube of 1
14	150	32-128	Tube of 1
14	300	32-328	Tube of 1
14	400	32-428	Tube of 1
15	150	32-130	Tube of 1
16	150	32-132	Tube of 1
16	300	32-332	Tube of 1
16	400	32-432	Tube of 1
18	160	32-136	Tube of 1
18	400	32-436	Tube of 1
19	160	32-138	Tube of 1
20	160	32-140	Tube of 1
20	300	32-340	Tube of 1
20	400	32-440	Tube of 1
22	160	32-144	Tube of 1
22	300	32-344	Tube of 1
25	160	32-150	Tube of 1
25	300	32-350	Tube of 1
25	400	32-450	Tube of 1