

Product Specification



LG

Model
43UP751C



Display

Screen size: 43 "

Screen Type: 4K Ultra HD LED

Resolution: 3840 x 2160

Image Ratio: 16: 9

Motion / Refresh Rate: Refresh Rate 50Hz

HDR Type: HDR10 +, HLG

Receiver: DVB-T2 / C / S2

Speaker

Speaker power: 20 W

Speaker system: 2.0 ch

Connectivity

2x HDMI

1xUSB

Ethernet (LAN)

1x Digital Audio Output (Optical)

2 (RF, Sat)

CI Slot

WiFi

Bluetooth

Additional Features

webOS Smart TV

Hotel Mode

Airplay 2

Time Shift

Google Assistant

Amazon Alexa

EPG

Teletext

Real 4K UHD

The LG UHD AI ThinQ always exceeds your expectations. Enjoy vibrant picture quality and vibrant colors with four times the pixel accuracy of Full HD.

Welcome to your new home

The days of endlessly searching for new content or your old favorites are over. The home screen has been redesigned to show you everything worth watching, all in one place. Enjoy personalized content suggestions based on tracking history, quick access to a variety of content, and easier control of connected devices.

Bring the cinema home

FILMMAKER MODE and HDR offer you a more exciting viewing experience. Connect to your favorite streaming platforms to access the content you love.

Home for all your favorites

Access the Netflix and Apple TV applications. Choose from the latest movies, TV shows, documentaries and live sports and find them all in one place.

Exciting sports experience

Feel like you are on the field. Bluetooth Surround Ready lets you try the game as if you were on the podium.

Clear advantage at home

Easily connect Bluetooth speakers for a true wireless surround sound experience. All the action sounds richer and more realistic, bringing the atmosphere of the big game to your living room.

See everything in 4K

The LG UHD AI ThinQ converts 2K content to the most vivid 4K image, improving detail, sharpness and color. Enjoy much clearer text and images with reduced noise and improved sharpness.

Dimensions

Size W/O Carton, W/O Stand 973 x 572 x 85

Size W/O Carton, With Stand 973 x 611 x 187

Size W/ Carton, With Stand 1060 x 660 x 152

VESA 200 x 200