

# Product Data Sheet



**Safety Products**



**Product name:** A2B2E2K2

**Part number:** A168097

## Characteristics

Standard: EN 141  
Thread connection: EN 148  
Pressure drop: 113 Pa  
Weight: 279 g  
Dimensions: ø107 x 67mm  
Colour: Silver

## Materials

Housing: Coated aluminium  
Adsorbent: Activated carbon, ABEK-type  
Sealing caps: Polyethylene

## Storage conditions

Temperature: -30°C to +70°C  
Relative Humidity: < 90%  
Expiry date: See canister bottom

**Usage:** Organic gases and vapours; Anorganic gases and vapours; Acid gases and vapours; Ammonia and ammonia derivatives

## Limitations for use:

**Do not use where the oxygen level in the atmosphere is less than 17%**

***Do not use with organic gases and vapours with a boiling point below 65°C***

**Applications:** Full Face and Half Masks with EN148 connection, Compact Air (Plus).

## Note:

The maximum mass of filter(s) designated to be used directly connected to a half mask is 300gr. (EN143).

The maximum mass of filter(s) designated to be used directly connected to a full face mask is 500gr. (EN143).

Packaging: 4 filters in a carton./4 cartons in a box./ 16 filters in a box  
Dimensions /Weight : 48x 24.5x 23.5cm / 05.6kg