

Compost Thermometers

6.35 and 7.94 mm ($\frac{1}{4}$ and $\frac{5}{16}$ ")
Diameter Stems

A36P-0-200F
shown smaller
than actual size.



Composter checks interior temperature of windrow.

Rugged, All Stainless Steel Construction
Hermetically Sealed, Will Not Fog
Pointed Stem for Easy Insertion
Easy-to-Read 76 mm (3") Diameter Dial
Exterior Reset Adjustment
6.35 mm ($\frac{1}{4}$ ") Diameter Stem or Sturdier 7.94 mm ($\frac{5}{16}$ ") Diameter Stem
Stem Lengths up to 1.8 m (6') Long
Available with °F, °C or Dual Scales

The OMEGA® compost thermometers are ideally suited for monitoring interior temperatures of compost piles and windrows. The clear, easy-to-read dial, with the pointer directly driven by the sensitive bi-metal helix in the bottom of the stem, gives an accurate reading every time. These hardy thermometers are used by composters everywhere for such applications as waste disposal, recycling, and mushroom farming.

Specifications

Crystal: Unbreakable plastic

Stem: 304 stainless steel

Head and Bezel: Polished type 302 stainless steel

Dial: Anodized aluminum

Accuracy: $\pm 1\%$ of full scale

Maximum Head Temperature: 93°C (200°F)

Dimensions: 76 mm (3") diameter dial; 6.35 mm ($\frac{1}{4}$ ") or 7.94 mm ($\frac{5}{16}$ ") diameter stem

Fahrenheit	
Range	Div
0 to 100°F	1°
25 to 125°F	1°
-40 to 160°F	2°
0 to 200°F	2°
0 to 250°F	2°

Celsius	
Range	Div
0 to 50°C	$\frac{1}{2}$ °
0 to 100°C	1°
-10 to 110°C	1°

Dual	
Range	Div
-20 to 120°C 0 to 250°F	2°

To Order

Model No.	Description
A12P-(*)	6.35 mm ($\frac{1}{4}$ ") diameter, 0.30 m (1') long stem
A24P-(*)	6.35 mm ($\frac{1}{4}$ ") diameter, 0.61 m (2') long stem
A36P-(*)	6.35 mm ($\frac{1}{4}$ ") diameter, 0.91 m (3') long stem
A48P-(*)	6.35 mm ($\frac{1}{4}$ ") diameter, 1.2 m (4') long stem
A12PF-(*)	7.94 mm ($\frac{5}{16}$ ") diameter, 0.30 m (1') long stem
A24PF-(*)	7.94 mm ($\frac{5}{16}$ ") diameter, 0.61 m (2') long stem
A36PF-(*)	7.94 mm ($\frac{5}{16}$ ") diameter, 0.91 m (3') long stem
A48PF-(*)	7.94 mm ($\frac{5}{16}$ ") diameter, 1.2 m (4') long stem
A60PF-(*)	7.94 mm ($\frac{5}{16}$ ") diameter, 1.5 m (5') long stem
A72PF-(*)	7.94 mm ($\frac{5}{16}$ ") diameter, 1.8 m (6') long stem

* Specify temperature range from tables above.

Ordering Examples: **A36P-0-250F/-20-120C**, compost thermometer with 6.35 mm ($\frac{1}{4}$ ") diameter, 0.91 m (36") stem, 0 to 250°F/-20 to 120°C dual scale temperature range.

A36PF-0-250F/-20-120C, compost thermometer.