

# Product data sheet

Specifications



## SELECTOR SWITCH 600VAC 10A 30MM T-K



9001KS43K10H1

### Main

|                           |                         |
|---------------------------|-------------------------|
| Range of product          | Harmony 9001K           |
| Product or component type | Selector switch         |
| Device short name         | K                       |
| Type of operator          | maintained              |
| Operator profile          | Black key operated knob |

### Complementary

|                               |                                                                                     |
|-------------------------------|-------------------------------------------------------------------------------------|
| Bezel material                | Chromium plated metal                                                               |
| Mounting diameter             | 30 mm                                                                               |
| Operator position information | 3 positions                                                                         |
| Connections - terminals       | Screw-clamp terminals, 1 x 0.22...2 x 1.5 mm <sup>2</sup> conforming to IEC 60947-1 |
| Device presentation           | Complete product                                                                    |

### Environment

|                           |                                                                   |
|---------------------------|-------------------------------------------------------------------|
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13                                           |
| Product certifications    | CE<br>UL listed file E42259 CCN NKCR<br>CSA LR24590 class 3211 03 |

### Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Weight             | 217.724 g |
| Package 1 Height             | 16.129 cm |
| Package 1 width              | 6.35 cm   |
| Package 1 Length             | 40.968 cm |

### Offer Sustainability

|                          |                                                                                                   |
|--------------------------|---------------------------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product                                                                             |
| REACH Regulation         | <a href="#">REACH Declaration</a>                                                                 |
| EU RoHS Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |

---

|                                   |                                                                                                                                                                                                                                                                                                                                                                        |
|-----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Mercury free</b>               | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| <b>RoHS exemption information</b> | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                    |
| <b>China RoHS Regulation</b>      | <a href="#">China RoHS declaration</a>                                                                                                                                                                                                                                                                                                                                 |
| <b>Environmental Disclosure</b>   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                          |
| <b>WEEE</b>                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins                                                                                                                                                                                                                                            |
| <b>California proposition 65</b>  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

---