

SDIS 0.6X3.5X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm
Order No.	2749810000
Type	SDIS 0.6X3.5X100
GTIN (EAN)	4050118897012
Qty.	1 pc(s).

SDIS 0.6X3.5X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	205 mm	Width (inches)	8.071 inch
Net weight	34 g		

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.6x3.5x100
------------------------	--

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.6 mm
Blade type	B	Blade width (B)	3.5 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ECLASS 9.0	21-04-04-07
ECLASS 9.1	21-04-04-07	ECLASS 10.0	21-04-04-07
ECLASS 11.0	21-04-04-07		

Downloads

Catalogues	Catalogues in PDF-format
------------	--