

Direct Plug-In/Contact Centre Headsets



TECHNICAL DATA

Microphone:

Directivity:	Unidirectional
Impedance:	1.0kΩ
Sensitivity:	-49±3dB (0dB=1V/Pa)
Frequency Range:	100-16,000Hz
Operating Temp:	-20°C~+60°C
Storage Temp:	-25°C~+70°C

Speaker:

Size:	ø30 mm
Input Power:	50 mW (1.26V)
Max Power:	100 mW (1.79V)
Impedance:	32Ω ±10% at 1kHz, 0.18V
Sound Pressure:	122±3dB at 1kHz
Resonance Frequency:	150±30 (20%) Hz
Frequency Range:	20Hz ~ 20,000Hz
Operating Temp:	-25°C ~ +50°C
Storage Temp:	-25°C ~ +50°C



USB-A



LEATHERETTE CUSHION



Commander

Universal 'Plug & play' USB professional office and contact centre headset, compatible with all major softphones. Fitted with 60mm leatherette ear cushions and padded T-bar, suitable for regular phone users.

Overview

Features	Single or dual speakers
	Left / right speaker side compatible
	Stereo audio sound for music and mono audio for speech
	Surround Shield™ noise cancelling microphone
	Fully flexible microphone for exact positioning
	270° adjustable microphone boom
	'Put and stay' ratchet microphone boom arm
	Swivel T-bar with padded leatherette cushion
	Overhead, sure-fit fully adjustable headband
What's included	Headset fitted with 60mm leatherette ear cushions and supplied with Quick Start Guide
Headset Weight	~ 62g / ~ 82g
Connection	USB-A direct plug-in
Certifications	UKCA, CE, FCC, RoHS, REACH
Warranty	2 Years repair or replacement warranty
MOQ	Master Shipping Carton: 40
EAN:	Commander-1: 5060126958659, Commander-2: 5060126958673
SKU:	Commander-1: 575-344-001, Commander-2: 575-344-002

In-line Control Features

3 button in-line control with volume and mute
'Plug & Play' solution - No software download needed

User will know the buttons by feel as each button will feel different

Ribbing on the side of the control box to indicate the direction of the buttons

Red LED illumination when mute is in use