



Ask for our full detailed catalog of COAXIAL BETWEEN SERIES ADAPTERS 50 & 75 Ω\* : **D1 191 CE**.

Interface	SMA		SMA 3.5		SMB		SMC		FME
	Male	Female	Male	Female	Male	Female	Male	Female	Male
<b>N Male</b>	R191 325 000 R191 325 500* (SMA Push-on)	R191 329 000 R191 329 500* (SMA Push-on)	R191 324 000	R191 328 000	R191 233 000		R191 141 000		
<b>N Female</b>	R191 327 000	R191 331 000	R191 326 000	R191 330 000	R191 236 000 (flange)	R191 239 000	R191 143 000	R191 147 000	R191 042 000

Interface	BNC		N 75 Ω / BNC 75 Ω		TNC		N 75 Ω / 1.6 / 5.6 (75 Ω)		DIN 7/16	
	Male	Female	Male	Female	Male	Female	Male	Female	Male	Female
<b>N Male</b>	R191 417 000 R191 417 500* (BNC Push-on)	R191 421 000 R191 421 500* (BNC Push-on)	R192 417 000	R192 421 000		R191 513 000	R192 775 000 (screw-on)	R192 777 000 (screw-on snap-on)	R191 721 000	R191 720 000
<b>N Female</b>	R191 419 000	R191 422 000 (bulkhead)	R192 419 000	R192 418 000	R191 511 000	R191 514 000 (flange)	R192 770 000 (screw-on)	R192 771 000 (screw-on snap-on)	R191 722 000	R191 723 000

Interface	C		LC		UHF		HN		N18 / PC 7 (18 GHz)	
	Male	Female	Male	Female	Male	Female	Male	Female		
<b>N Male</b>		R191 703 000				R191 731 000			R191 025 000	Measurement kit (M + F) R191 094 000
<b>N Female</b>	R191 705 000	R191 708 000 (flange)	R191 745 000	R191 741 000	R191 733 000		R191 737 000	R191 027 000		

\* For Push-on adapters, please ask for **D1 036 DE** catalog. Numerous other models for panel mount also currently available  
 • Upon request