Note: All part numbers are RoHS Compliant.


Metal-Shell CPC Connector Accessories


Cable Clamps

Material and Finish

Body and Clamp Halves—Zinc alloy, nickel plated

Screws and Washers—Stainless steel






Shell Size	Dimensions A	B	C	Cable O.D. Range	Thread Size	Part No.
14	**.938** 23.83	**1.175** 29.85	**1.165** 29.59	**.225-.562** 5.71-14.27	7/8-20 UNEF-3B	208945-5
22	**.938** 23.83	**1.432** 36.37	**1.469** 37.31	**.325-.750** 8.26-19.05	1-3/16-18 UNEF-3B	208945-7
28	**1.031** 26.19	**1.593** 40.46	**1.688** 42.88	**.450-.938** 11.43-23.83	1-7/16-18 UNEF-3B	208945-8


Notes: 1. For Shell Size 22 Receptacle use plastic cable clamp Size 17 (See page 38), for Shell Size 28 Receptacle use plastic cable clamp Size 23 (See pages 38-39). Use Size 14 metal cable clamp for both plug and receptacle Size 14 connectors.
2. Metal cable clamps (Sizes 22 and 28) are for use with Metal-Shell CPC plugs ONLY.


Cable Entry Seals

Heat Shrinkable Sealing Boots

Cable entry seals are used with jacketed cable to provide an environmentally sealed wire-to-connector system. They can be used with plugs.







Thick Wall Boots

Material

Internal Sleeve—Nylon

Outer Tubing—Polyolefin, black


Shell Size	Dimensions A	B	Expanded Wall Thickness	Sealing Range (Dia.)	Max. Recovered Inside Dia.	Part No.
22	**3.000** 76.20	**1.250** 31.75	**.070** 1.78	**.550 - 1.250** 13.97 - 31.75	**.500** 12.70	54012-3
28						54012-4


Protective Cap Assemblies (for Metal-Shell CPC Receptacles Only)

Material and Finish

Zinc alloy, nickel plated

Shell Size	Dimensions A	B	Part No.
14	**1.225** 31.11	**.515** 13.08	213823-2
22	**1.750** 44.45	**.635** 16.13	211903-1
28	**2.170** 55.12	**.635** 16.13	211904-1





Catalog 82021
Revised 7-07

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752
Canada: 1-905-470-4425
Mexico: 52-55-1106-0800
C. America: 57-1-254-4444

South America: 55-11-2103-6000
Hong Kong: 852-2735-1628
Japan: 81-44-844-8013
UK: 44-208-420-8341