

4000 Series Tamperproof Outlet

SPECIFICATION

WIDTH	87mm
DEPTH	27mm
HEIGHT	105mm
SPACER PLATE DEPTH	8mm
MATERIAL	ABS thermoplastic resin, with grade UL94 VO at 1.5mm flame retardancy
FINISH	High Gloss
IDC BLOCKS	4 Way Industry Standard IDC blocks
PCB	1.6mm double sided PTH Boards
CONFORMS TO	TIA/EIA-568-B Enhanced Category 5 Specification

SIMPLE ASSEMBLY SEQUENCE



WHAT IS ENHANCED CATEGORY 5?

Enhanced Category 5 is a Specification designed for data networks to support very high-speed data transmission, like Gigabit Ethernet, at a bandwidth of 100MHz.

ORDERING INFORMATION

Product Description

4030, 4 Way Tamperproof Wall Outlet

Part Number

5506TP