

LIDO-640 WBP

6.5" Waterproof 2-way Passive Wall-Mount Speaker Pair, Black

LIDO series is specifically designed for both indoor and outdoor applications in projects with constant voltage or low impedance systems. Thanks to the IP65 protection rating, to the PP woofers, to the UV-resistant PP cabinets, to the stainless-steel metal parts, and to the aluminum grille, these speakers do not fear the rigors of exposure to atmospheric agents.

The high excursion custom transducers guarantee a clear and defined sound, always providing a higher audio quality even at high sound pressures. The power-tap selector allows you to select 3 powers and adapt the speaker to 100V or low impedance systems. The C-bracket allows you to adjust the horizontal (+55°/-55°) and vertical position (+20°/-20°).



PRODUCT DETAILS

Key features

2-Way Passive system with 40W RMS Power

IP65 Protection Rating for Outdoor/Indoor Applications

UV-Resistant PP Housing

Built-in 100V Line Transformer

Power Tap Selector for 100V or low-impedance systems

Horizontal and Vertical adjustable C-Bracket

Paintable Housing and Grille

Specifications

Speaker Type	2-Way Passive
IP Rating	IP65
RMS Power (@ 8ohm)	40W
70V Powers	5W - 10W - 20W
100V Powers	20W - 30W - 40W
Frequency Response (-10dB)	65Hz-18kHz
Sensitivity (1w@1m)	92dB
Impedance	8ohm
Woofers	6.5" (165mm), PP cone
Tweeter	0.5" (13mm), Mylar dome
Housing	UV-Resistant PP, paintable
Bracket	C-Bracket with Pan/Tilt adjustable angle and stainless steel screws
Grille	Perforated aluminum, powder coated paint, acoustic transparent foam inside, paintable
Color	Nero
Product Size (WxDxH)	205 x 182 x 328mm
Speaker Weight (single unit)	3,475 kg
Packing Size (WxDxH) (pair)	465 x 245 x 365 mm
Packing Weight (pair)	8,2 kg