



ANSMANN Lithium 4

- Charger for up to 4 Li-Ion rechargeable batteries (3.6V/3.7V) / LiFePO4 (3.2V) 26650, 22650, 18650, 18500, 17670, 16340, 14500 etc. or 1-4 NiMH rechargeable batteries (1.2V) / AAA / AA or 1-2 Sub C
- Includes a USB type-C charging cable
- Single slot monitoring
- Automatic detection of Li-Ion and NiMH rechargeable batteries, manual selection of LiFePO4 rechargeable batteries
- Charging starts automatically once the batteries have been inserted with the correct polarity
- Microcontroller-monitored charging control (CC-CV with Li-Ion/LiFePO4, 0dV/-dV with NiMH)
- Temperature monitoring of each individual slot, regardless of the battery type
- Automatic battery-full detection and termination of the charging process
- Trickle charging for NiMH rechargeable batteries
- Display of the charging status and the battery parameters via the LCD
- Indication of incorrectly inserted batteries (wrong polarity)
- Operation via a 5V DC USB adapter (not included)

INFORMATION

Product name	Lithium 4
Part No.	1001-0122
EAN-Code	4013674183562
Customs tariff number	8504405900
Product content	Lithium 4 charger, USB type-C charging cable, operating instructions

Product	129,5 × 96 × 33 mm / 0 g
Packing + Product	133 × 120 × 38 mm / 250 g
Packing Unit	40 (552 × 260 × 220 mm)

