

113A.8C | 113A.C - Chromed adjustable wrenches





Standards:

NF ISO 6787, ISO 6787, DIN 3117, ASME B107.100

Description:

- Tool equipped with a FACOM SLS attachment solution, preventing any risk of accidental falls.
- Good access to the button = easy setting.
- Non-protruding moving jaw at maximum capacity.
- Pre-adjustment of jaw opening thanks to millimetric gradation.
- Right-hand button rotation.
- Range from 4" to 24".
- Presentation: chromed body and polished head faces.
- Clés à molette avec trou dans le manche : accrochage directe par mousqueton.



	113A.8C
A [mm]	27.0
A [in]	
Length L [mm]	206.0
Thickness E [mm]	6.5
Thickness E1 [mm]	13.5
Thickness E2 [mm]	9
Thickness E4 [mm]	8.5
Head Height C [mm]	18.5
Head Width B [mm]	61.5
Weight [Kg]	0.275