

256 - Precision centre punches




Standards:

NF E 71-211, DIN 7250, ASME B107.410

Description:

- Chrome-vanadium steel forged, hardened to 52 to 58 HRc.
- Presentation: knurled body.
- Zinc-plated finish.

	A [mm]	Length L [mm]	Diameter [mm]	Weight [g]
256.10	10.0	130.0	14.0	135.0
256.2.5	2.5	100.0	7.0	25.0
256.4	4.0	105.0	8.0	35.0
256.6	6.0	115.0	10.0	60.0
256.6PB	6.0	115.0	10.0	60.0
256.8	8.0	130.0	12.0	100.0