

## 467B.11 | 467B - Metric ratchet combination wrenches




### Standards:

NF ISO 1711-1, NF ISO 691, ISO 1711-1, ISO 691, DIN ISO 1711-1, DIN ISO 691

### Description:

- Ultra-Grip ratchet wrenches: retaining pin on the ring + securing notch on the open end. Does not slip on the nuts, optimum safety.
- Compact ratchet mechanism reversing by lever. Better accessibility.
- 5° increments (7.5° for size 6 mm; 6° for 7, 8 and 9 mm sizes). Enhanced productivity.
- Ring and open end tilted at 15°.
- Metric sizes: 6 to 41 mm
- Satin chrome finish.



	<b>467B.11</b>
A [mm]	11.0
A [in]	
Length L [mm]	165.0
Thickness E [mm]	5.2
Thickness E1 [mm]	7.7
Thickness E2 [mm]	3.5
Head Height C [mm]	10.6
Head Width B [mm]	23.7
Head Width B1 [mm]	22.0
Weight [Kg]	0,058