

J.10LA | J.LA - 3/8" long-reach metric 12-point sockets



Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Long-reach sockets for long recess or thread access.
- Available as rack sets (Ref JL.40U).
- Finish: bright chrome.

	J.10LA
A [mm]	10.0
Diameter [mm]	17.3
Diameter D1 [mm]	14.5
Length L [mm]	55.0
Length L1 [mm]	9.0
12-Point [mm]	12.0
Weight [g]	50.0