

R.304DA | 306D - Click wrenches without accessories




Standards:

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description:

- Factory accuracy: $\pm 2\%$ except: - R.306-25D - K.306A600 - K.306A1000 ($\pm 4\%$). - R.304DA ($\pm 6\%$).
- Reliability of mechanism: 50 000 cycles (wrenches up to 200 N.m).
- Use possible with accessories: - End fitting: 9 x 12 or 14 x 18 mm. - Diameter: 30 mm.
- One-way wrenches usable for unscrewing by reversing the bits.
- Numbered wrenches supplied with ISO 6789 calibration certificate.
- Supplied in plastic box.

|  | R.304DA |
|--|---------|
| Length L [mm] | 185.0 |
| Attachement ["] | 9 x 12 |
| Capacity [Nm] | 1 - 5 |
| Graduation [Nm] | 0.05 |
| Weight [Kg] | 0.29 |