

185A.20VE | 185A-195A.VE - 1,000 Volt insulated long half-round nose pliers



Standards:

NF ISO 5745, ISO 5745, DIN ISO 5745, ASME B107.500, NF EN 60900, EN 60900, DIN EN 60900

Description:

- For your safety, all pliers are tested individually at 10,000 volts for 10 seconds, at the end of the manufacturing cycle.
- Slim, fine serrated noses.
- Lateral wire cutter for copper and hard steel wire.
- 185A.20VE: straight nose.
- 195A.20VE: 40° angled nose.
- Return spring.
- Ergonomic anti-slip grips.
- Finish: polished, varnished.

	185A.20VE
Diameter [mm]	2.9
Length L [mm]	200.0
Thickness E [mm]	3.6
Thickness E1 [mm]	9.0
Head Height C [mm]	75.0
Head Width B [mm]	18

