

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [Harsh/Wet Environment Fans](#) > 11938MA-24L-ET-D0[← Back To Harsh/Wet Environment Fans](#)

Have a question about this product?


[Ask Our Experts →](#)

## Harsh/Wet Environment Fans - 11938MA-24L-ET-D0

[Get a sample](#)

### Resources

[Specification Sheet](#)[Series  
Data  
Sheet](#)



Specifications

|                   |                            |
|-------------------|----------------------------|
| Category          | Harsh/Wet Environment Fans |
| Part Number       | 11938MA-24L-ET-D0          |
| Frame Width [mm]  | 119                        |
| Frame Height [mm] | 119                        |
| Frame Depth [mm]  | 38                         |

|                                      |                           |
|--------------------------------------|---------------------------|
| <b>Max. Air Flow [CFM]</b>           | 122.19                    |
| <b>Max. Air Flow [m3 per min]</b>    | 3.46                      |
| <b>Max. Static Pressure [In H2O]</b> | 0.41                      |
| <b>Max. Static Pressure [Pa]</b>     | 102                       |
| <b>Fan Speed [RPM]</b>               | 3200                      |
| <b>Noise [dB]</b>                    | 49.5                      |
| <b>Life Expectancy [L10]</b>         | 25 degree C 100,000 Hours |
| <b>Bearing Type</b>                  | Ball Bearing              |
| <b>Nominal Voltage [V]</b>           | 24                        |
| <b>Operating Voltage - Lower [V]</b> | 15                        |
| <b>Operating Voltage - Upper [V]</b> | 27.6                      |
| <b>Current [A]</b>                   | 0.35                      |
|                                      |                           |

|                            |             |
|----------------------------|-------------|
| Input Power [W]            | 8.4         |
| Mass [g]                   | 400         |
| IP Rating                  | IP68/IP69K  |
| Tach / Locked Rotor Output | Tach Output |
| Status                     | Active      |

PRODUCTS

[See All Products](#) →

[Find A Distributor](#)

[Find a Sales Representative](#)

INDUSTRIES

[See All Industries](#)

[Automotive](#)

[Industrial](#)

[Medical](#)

[Consumer Technology](#)

[Smart City](#)

[Lighting Innovations](#)

RESOURCES

[See All Resources](#) →

[Application Notes & Whitepapers](#)

[Latest News](#)

[Videos](#)

CONTACT

NMB Technologies Corporation

[\(248\) 919-2250](#)

[info@nmbtc.com](mailto:info@nmbtc.com)

Have A Question?

Our precision component experts can help you find the right solutions.

[Contact Us Today](#)

[Find A Distributor](#)

[Find Sales Rep For Fans](#) →

NMB Technologies Corporation © 2021. All Rights Reserved.

[Company](#)

[Careers](#)

[Sitemap](#)

[Privacy  
Policy](#)

[Terms of  
use](#)