

[Update related to COVID-19. Learn More →](#)[Products](#)[Industries](#)[About](#)[Resources](#)[Blog](#)[Contact us](#)[Find A Distributor](#)[Home](#) > [Products](#) > [Cooling Fans](#) > [DC Axial Fans](#) > [04020VA-12M-AL-00](#)[← Back To DC Axial Fans](#)

Have a question about this product?

[Ask Our Experts →](#)

DC Axial Fans - 04020VA-12M-AL-00

[Get a sample](#)

Resources

Specification Sheet	Series Data Sheet
Certificates	RoHS Certificate
CAD Files	04020VA.stp
CAD Files	04020VA.sldprt



CAD Files	04020VA.prt
CAD Files	04020VA.iges



Specifications

Category	DC Axial Fans
Part Number	04020VA-12M-AL-00
Legacy Part Number	1608VL-04W-B49-B00
Frame Width [mm]	40
Frame Height [mm]	40

Frame Depth [mm]	20
Max. Air Flow [CFM]	8.8
Max. Air Flow [m3 per min]	0.25
Max. Static Pressure [In H2O]	0.24
Max. Static Pressure [Pa]	58.8
Fan Speed [RPM]	7500
Noise [dB]	29
Life Expectancy [L10]	25 degree C 100,000 Hours
Bearing Type	Ball Bearing
Nominal Voltage [V]	12
Operating Voltage - Lower [V]	7
Operating Voltage - Upper [V]	13.2