

Update related to COVID-19. Learn More →



Products

Industries

About

Resources

Blog

Contact us

Find A Distributor

Home > Products > Cooling Fans > DC Axial Fans > 11925SA-12P-EA-D0

← Back To DC Axial Fans

Have a question about this product?



DC Axial Fans - 11925SA-12P-EA-D0

Get a sample

Resources

| | |
|---------------------|-------------------|
| Specification Sheet | Series Data Sheet |
| Certificates | RoHS Certificate |





Specifications

| | |
|--------------------------|-------------------|
| Category | DC Axial Fans |
| Part Number | 11925SA-12P-EA-D0 |
| Frame Width [mm] | 119 |
| Frame Height [mm] | 119 |
| Frame Depth [mm] | 25 |

| | |
|--------------------------------------|---------------------|
| Max. Air Flow [CFM] | 102.05 |
| Max. Air Flow [m3 per min] | 2.89 |
| Max. Static Pressure [In H2O] | 0.243 |
| Max. Static Pressure [Pa] | 60.5 |
| Fan Speed [RPM] | 2800 |
| Noise [dB] | 40.5 |
| Life Expectancy [L10] | 40,000 hours at 60C |
| Bearing Type | Ball Bearing |
| Nominal Voltage [V] | 12 |
| Operating Voltage - Lower [V] | 7 |
| Operating Voltage - Upper [V] | 13.8 |
| Current [A] | 0.33 |

| | |
|-----------------------------------|--------|
| Input Power [W] | 3.96 |
| Mass [g] | 165 |
| Tach / Locked Rotor Output | No |
| Status | Active |

PRODUCTS[See All Products](#) →[Find A Distributor](#)[Find a Sales Representative](#)**INDUSTRIES**[See All Industries](#)[Automotive](#)[Industrial](#)[Medical](#)[Consumer Technology](#)[Smart City](#)[Lighting Innovations](#)**RESOURCES**[See All Resources](#) →[Application Notes & Whitepapers](#)[Latest News](#)[Videos](#)**CONTACT****NMB Technologies Corporation****(248) 919-2250****info@nmbtc.com**

Have A Question?

Our precision component experts can help you find the right solutions.

[Contact Us Today](#)[Find A Distributor](#)[Find Sales Rep For Fans](#) →

