Update related to COVID-19. Learn More ➜



# DC Axial Fans - 04010SA-12L-AA-D0

Get a sample

## Specifications

| | |
|---|---|
| **Category** | DC Axial Fans |
| **Part Number** | 04010SA-12L-AA-D0 |
| **Frame Width [mm]** | 40 |

| | |
|---|---|
| **Frame Height [mm]** | 40 |
| **Frame Depth [mm]** | 10 |
| **Max. Air Flow [CFM]** | 4.9 |
| **Max. Air Flow [m3 per min]** | 0.14 |
| **Max. Static Pressure [In H2O]** | 0.11 |
| **Max. Static Pressure [Pa]** | 27.5 |
| **Fan Speed [RPM]** | 5500 |
| **Noise [dB]** | 21.5 |
| **Life Expectancy [L10]** | 50,000 hours at 40C |
| **Bearing Type** | Ball Bearing |
| **Nominal Voltage [V]** | 12 |
| **Operating Voltage - Lower [V]** | 10.2 |
| **Operating Voltage - Upper [V]** | 13.8 |

| | |
|---|---|
| **Current [A]** | 0.04 |
| **Input Power [W]** | 0.48 |
| **Mass [g]** | 16 |
| **Tach / Locked Rotor Output** | No |
| **Status** | Active |

NMB Technologies Corporation © 2021. All Rights Reserved.