tesa® Professional 4843



Product Information

Premium plastering protection tape to protect sensitive profiles and facings

The tesa® plastering protection tape won't let you down at any time of year, because the sturdy tape will stick reliably even when it's cold. This means it provides optimum protection for painting, stucco and plastering work. It comprises a supple, tear-resistant, soft PVC film and is coated with a special aging-resistant adhesive compound. The plastering masking tape protects the surfaces of sensitive profiles, frames and facing from soiling or damage through plastering material or tools. The tape is insensitive to humidity, weak acid and alkaline solutions as well as to many chemicals.

Main Application

- Outdoor applications
- Good protection of smooth and slightly rough surfaces
- For applications that require high adhesion power (e.g. plastering, painting, gypsum, masonry and stucco work)
- Also suitable for the sealing of bags, heavy duty wrapping and other DIY applications
- For temperatures above 0°C

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

lecinical Data			
Backing materialColorTotal thicknessType of adhesive	PVC film orange 122 μm natural rubber	 Elongation at break Tensile strength Temperature resistance short term UV-resistance 	200 % 23 N/cm 60 ℃ 2 weeks
Adhesion to			
• steel	1.2 N/cm		
Properties			
 Hand tearability 	•••	 Ageing resistance (UV) 	•
Easy to remove	yes	Humidity resistance	•••
Easy to write on	no	UV-resistance	••••
Suitable for rough surfaces	••••	Water resistance	•••
Paint anchorage	•••	 Fluorescent 	no
Sharp color edge	••••	Conformability	••••
Abrasion resistance	••••	Fogging	•••

Evaluation across relevant tesa® assortment: •••• very good ••• good •• medium • low



tesa® Professional 4843

Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit http://l.tesa.com/?ip=04843