

tesa® 60040 Industry Cleaner



Product Information

Multi-functional cleaning spray to thoroughly clean machines, tools and surfaces

tesa® Industry Cleaner 60040 is a versatile spray for fast and easy cleaning of machine and plastic parts, glass and metal surfaces. Cleaned surfaces allow for optimum bonding with tesa® adhesive tapes and spray glues.

- Removes even stubborn stains like wax, oil, grease, rubber debris and silicone residue
- Evaporates without leaving residues
- Excellent cleaning results on machinery and many different surfaces such as plastic and metal
- Spray reaches even concealed and hard-to-reach places
- Leaves a pleasant scent
- The cleaner is based on LIMONENE from natural sources
- Free from silicone

Main Application

- Cleaning machine and plastic parts, glass and metal surfaces * Ideal for more recessed and difficult to reach places * Preparation for the optimum usage of tesa® adhesive solutions * For a clean workshop

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

- | | | | |
|--------------------|--|---------------------------------------|----------------|
| • Color | transparent | • Propellant based on | propane/butane |
| • Solvent based on | dearomatized
special
petrol,isopropanol,limonene | • Recommended distance of
spraying | 20 cm |

Additional Information

- Observe the safety-information on the spray-can
- Shake can well before use
- Apply a generous coating to the surface to be cleaned and leave for a few moments to take effect
- Wipe off with a clean cloth
- Test sensitive materials for suitability first
- Contains > 30% aliphatic hydrocarbons and LIMONENE according to Decree (EC) no. 648/2004 on Detergents
- Refer to special instructions/safety data sheets: www.tesa.com/safety

tesa® 60040 Industry Cleaner

Product Information



Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=60040>