

tesa® Professional 4334 Precision Mask®



Product Information

High grade paint tape for precise and flat paint edges

The tesa® Precision Mask® 4334 reliably guarantees razor-sharp paint edges, and is extremely easy to use at the same time - thanks to the ideal combination of the special, supple backing and the perfectly balanced acrylic adhesive compound. This helps the tape to stick extremely flush to the surface and prevent paint tears. The combination of professional painting tape and your skilled expertise will result in paintwork to please your customers. In addition, the high quality of the painting tape will save you expensive touch-up work. The tesa® Precision Mask® 4334 is also recommended for masking applications during spray painting with afterwards oven drying up to 120°C/ 30min. Due to the thin and low elongating backing it is perfectly suited for two-tone applications, e.g. straight and long lines.

Features

- Indoor masking (up to 6 months)
- Outdoor masking (up to 8 weeks)
- For smooth and slightly textured surfaces
- For high-quality painting and lacquering work
- For spray painting with afterwards oven drying up to 120°C/30 min

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

• Backing material	Washi paper	• Elongation at break	4 %
• Color	yellow	• Tensile strength	30 N/cm
• Total thickness	90 µm	• UV-resistance	8 weeks
• Type of adhesive	acrylic		

Adhesion to

- steel 1.8 N/cm

Properties

• Hand tearability	●●●●	• Paint anchorage	●●●●
• Suitable for sensitive surfaces	●●●	• Sharp color edge	●●●●
• Suitable for rough surfaces	●●●	• Conformability	●●●●

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

tesa® Professional 4334 Precision Mask®



Product Information

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=04334>