

10ft (3m) HDMI 2.1 Cable 8K - Certified Ultra High Speed HDMI Cable 48Gbps - 8K 60Hz/4K 120Hz HDR10+ eARC - Ultra HD 8K HDMI Cable - Monitor/TV/Display - Flexible TPE Jacket

Product ID: HDMM21V3M



This 9.8 ft. (3 m) Ultra High Speed HDMI 2.1 Certified Cable withstands the daily demands of connecting your HDMI devices. Tested to endure strenuous wear and tear, this durable cable is a must-have for both business and consumer applications.

Experience the latest that HDMI 2.1 has to offer

This high performance 8K cable supports resolutions of up to 8K at 60Hz (7680x4620p), 5K at 60Hz, 4K at 120Hz and bandwidths of up to 48Gbps. It also supports HDR10+ (High Dynamic Range) and Dolby Vision for higher contrast ratio and vivid colors.

Plus, eARC (Enhanced Audio Return Channel) has up to 32 uncompressed 5.1 and 7.1 digital audio channels to support DTS-HD Master Audio, DTS:X, Dolby TrueHD, Dolby Atmos for high quality sound. Latest HDCP 2.3 encrypts and secures your video and audio content.

With higher resolutions, increased speeds, sharper images, and crystal-clear audio, you can expect an enhanced video experience. The cable is guaranteed to provide the very best HDMI 8K performance available today. It's the perfect cable for creating the ultimate home theater or for providing lifelike digital signage.

This cable works with all 8K ready devices and is also backward compatible with previous HDMI specifications.

Provide superior connections with Ultra High Speed certification

The cable has undergone rigorous compliance testing and is certified by an HDMI Authorized Test Center to ensure it supports the high bandwidth enabled features it promises. An EMI test is also performed to ensure the cable minimizes interference with wireless signals.

Cable Key Features

- Aluminum-mylar foil with braided shielding improve EMI protection

- Long lasting flexible TPE jacket & strain relief (TPE is non-toxic & halogen free for environmental sustainability)
- Insulated conductors reduce friction, provide more flexibility

Connector Key Features

- Die-cast aluminium sub-structure shielding improves signal integrity & prevents signal degradation
- Corrosion-free gold-plated connectors ensure premium video quality & enhanced reliability
- Tested to withstand 10,000+ insertions

The HDMM21V3M is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

Features

- **HIGH PERFORMANCE 8K CABLE:** 9.8 ft (3m) Ultra HD HDMI 2.1 cable; 8K/5K 60Hz, 4K 120Hz video (48Gbps); Dynamic HDR10+ & Dolby Vision for high contrast & vivid picture; eARC, DTS-HD Master Audio/DTS:X/Dolby TrueHD/Atmos for high quality audio; HDCP 2.3
- **ULTRA CERTIFIED CABLE:** Ultra High Speed HDMI 2.1 Certification ensures that each cable will deliver full 8K performance & beyond; Encased in die-cast aluminium shielding to improve signal integrity & prevent signal degradation due to EMI Interference
- **DURABLE:** UHD HDMI cord is tested to withstand 10,000+ insertions & 600+ bend cycles at 120; corrosion-free gold-plated connectors; Long lasting flexible TPE jacket & strain relief; TPE is non-toxic & halogen free for environmental sustainability
- **APPLICATIONS:** 8K HDMI cable is ideal for Commercial, AV Production & High-Res applications; For home, office, classroom; works w/ computer, laptop, desktop or workstation to connect your TV/monitor/display/projector; Samsung/Sony/Apple TV/Dell/LG;
- **SPECS:** 3m (9.8 feet) HDMI 2.1 Certified Ultra High Speed HDMI Cable 48Gbps HDMI Male to Male 6 mm (0.24") Outer Diameter, 30AWG TPE Jacket Al-Mylar Foil w/Braid EMI Shielding Works with HDMI 2.0b/2.0a/2.0/1.4 StarTech.com Lifetime Warranty

Hardware

Warranty	Lifetime
Active or Passive Adapter	Passive
Number of Conductors	19

Connector Plating	Gold
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Data Transfer Rate	48Gbps
Maximum Digital Resolutions	8K 60Hz (7680 x 4320)
Audio Specifications	HDMI - 32 Channel Audio HDMI - 7.1 Channel Audio

Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	0C to 50C (32F to 122F)
Humidity	0%RH ~ 85%RH

Physical Characteristics

Color	Gray and Black
Wire Gauge	30/32 AWG
Cable Length	9.8 ft [3 m]
Cable OD	0.2 in [6 mm]
Product Length	9.8 ft [3.0 m]
Product Width	0.8 in [20.0 mm]
Product Height	0.4 in [11.2 mm]
Weight of Product	5.2 oz [147.0 g]

Packaging Information



Package Length	7.9 in [20.0 cm]
Package Width	7.7 in [19.5 cm]
Package Height	0.8 in [19.8 mm]
Shipping (Package) Weight	5.5 oz [157.0 g]

What's in the Box

Included in Package	Ultra High Speed HDMI Cable
---------------------	-----------------------------

****Product appearance and specifications are subject to change without notice.***

