

6ft (2m) Premium Certified HDMI 2.0 Cable - High Speed Ultra HD 4K 60Hz HDMI Cable with Ethernet - HDR10, ARC - UHD HDMI Video Cord - For UHD Monitors, TVs, Displays - M/M

Product ID: HDMMV2M



This 6.6 ft. (2 m) Premium High Speed HDMI 2.0 Certified Cable withstands the daily demands of connecting your HDMI devices. Tested to endure strenuous wear and tear, this durable cable is a must-have for both business and consumer applications.

Experience the latest that HDMI 2.0 has to offer

This high performance 4K cable supports resolutions of up to 4K at 60Hz (3840x2160p) and bandwidths of up to 18Gbps. It also supports HDR10 (High Dynamic Range) and Dolby Vision for higher contrast ratio and vivid colors.

Plus, ARC (Audio Return Channel) has up to 32 uncompressed 5.1 and 7.1 digital audio channels to support DTS-HD Master Audio, DTS:X, Dolby TrueHD, Dolby Atmos for high quality sound.

With high resolutions, increased speeds, sharper images, and crystal-clear audio, you can expect an enhanced video experience. The cable is guaranteed to provide the very best HDMI 4K performance available today. It's the perfect cable for creating the ultimate home theater or for providing lifelike digital signage.

This cable works with all 4K ready devices and is also backward compatible with previous HDMI specifications.

Provide superior connections with Premium High Speed certification

The cable has undergone rigorous compliance testing and is certified by an HDMI Authorized Test Center to ensure it supports the high bandwidth enabled features it promises. An EMI test is also performed to ensure the cable minimizes interference with wireless signals.

Cable Key Features

Aluminum-mylar foil with braided shielding improve EMI protection

Long lasting flexible TPE jacket & strain relief (TPE is non-toxic & halogen free for environmental sustainability)

Connector Key Features

Corrosion-free gold-plated connectors ensure premium video quality & enhanced reliability

Tested to withstand 10,000+ insertions

The HDMMV2M is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

Features

- **HIGH PERFORMANCE CABLE:** 6.6ft (2m) Premium Certified High Speed HDMI cable with Ethernet supports 4K 60Hz (3840x2160), 18Gbps bandwidth, HDR10, Ultra wide aspect ratio, 32 Ch Audio (5.1/7.1/Dolby TrueHD/Atmos), ARC, BT.2020 colorimetry, 3D video
- **PREMIUM HDMI 2.0 CABLE:** Ultra HD 4K 60Hz HDMI cable is engineered & built to improve signal integrity; Featuring corrosion free gold-plated connectors encased in die-cast aluminum to prevent signal degradation due to EMI
- **DURABLE:** Tested to withstand 10,000+ insertions & 600+ bend cycles at 120 angle; Long lasting TPE jacket with molded soft TPE strain relief absorbs stress of frequent bends; TPE is non-toxic, halogen free & RoHS certified for environmental sustainability
- **APPLICATIONS:** Ideal for home/office & travel, works with computer/laptop/desktop/PC/workstation; UHD HDMI cord to connect your TV/monitor/display/projector; Samsung/Sony/Apple TV/Dell/LG; Works w/ HDMI 2.0 Ultra HD, 1080p Full HD & previous HDMI versions
- **SPECS:** 6.6 feet (2 meter) HDMI 2.0 Premium Certified HDMI Cable High Speed Cable with Ethernet HDMI Male to Male 6 mm (0.24") Outer Diameter, 30AWG Jacket: TPE EMI Shield: Al-Mylar Foil, Braid StarTech.com Lifetime Warranty

Hardware

| Warranty | Lifetime |
|---------------------------|--------------------------------|
| Active or Passive Adapter | Passive |
| Number of Conductors | 19 |
| Connector Plating | Gold |
| Cable Jacket Material | TPE - Thermoplastic Elastomers |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

Performance

| | |
|-----------------------------|--------------------------|
| Video Revision | HDMI 2.0b |
| Maximum Data Transfer Rate | 18Gbps |
| Maximum Cable Length | 6.6 ft [2 m] |
| Maximum Digital Resolutions | 4K 60Hz 3840x2160 |
| Audio Specifications | HDMI - 32 Channel Audio |
| | HDMI - 7.1 Channel Audio |
| | HDMI - 5.1 Channel Audio |

Connector(s)

| | |
|-------------|---------------|
| Connector A | HDMI (19 pin) |
| Connector B | HDMI (19 pin) |

Environmental

| | |
|-----------------------|-------------------------|
| Operating Temperature | 0C to 50C (32F to 122F) |
| Storage Temperature | 0C to 50C (32F to 122F) |
| Humidity | 0%RH ~ 85%RH |

Physical Characteristics

| | |
|-------------------|------------------|
| Color | Gray and Black |
| Wire Gauge | 30 AWG |
| Cable Length | 6.6 ft [2 m] |
| Cable OD | 0.2 in [6 mm] |
| Product Length | 6.6 ft [2.0 m] |
| Product Width | 0.8 in [20.0 mm] |
| Product Height | 0.4 in [10.0 mm] |
| Weight of Product | 3.9 oz [110.0 g] |

Packaging Information



| | |
|------------------------------|------------------|
| Package Length | 8.7 in [22.0 cm] |
| Package Width | 7.9 in [20.0 cm] |
| Package Height | 0.4 in [10.0 mm] |
| Shipping (Package) Weight | 4.2 oz [120.0 g] |

What's in the Box

| | |
|---------------------|-------------------------------|
| Included in Package | Premium High Speed HDMI Cable |
|---------------------|-------------------------------|

****Product appearance and specifications are subject to change without notice.***

