

SENCITY® Rail Antenna 1399.99.0026

Description

Railway rooftop antenna for Tetra, DVB-T, 2G/3G/4G/5G cellular and Wi-Fi 4/Wi-Fi 6 bands.
 Multiple Antenna installations support Cellular and Wi-Fi MIMO.
 Embedded GNSS antenna with integrated LNA.
 Supports GPS L1, Galileo E1, BeiDou B1 and GLONASS G1.
 Rugged design, meets EN 50155 Railway Standard.
 Fire retardant according to EN 45545-2 and NFPA-130.
 Dedicated grounding contact (optional).
 Cable conduit support (optional).



Product Configuration

Technical Data

Electrical Data

	Band 1	Band 2	Band 3	Band 4
Frequency (MHz)	380 - 694	694 - 960	1350 - 1525	1710 - 2700
VSWR	1.8	1.8	1.5	1.5
Impedance (Ohm)	50	50	50	50
Gain (dBi)	3	4	7.5	7.5
Composite power max (W)	80	80	80	80
Ambient temperature (°C)	25	25	25	25

	Band 5	Band 6	Band 7	Band 8
Band Name				GNSS
Frequency (MHz)	2700 - 3300	3300 - 4900	4900 - 6425	1559 - 1610
VSWR	1.5	1.7	1.5	1.8
Impedance (Ohm)	50	50	50	50
Gain (dBi)	6.5	7	8	
Composite power max (W)	80	80	80	
Ambient temperature (°C)	25	25	25	

Ports

	Port 1	Port 2
Connector	N, jack (female)	TNC, plug (male)
Polarization	vertical	circular right
DC grounded	Yes	No

Connections

	Band 1	Band 2	Band 3	Band 4	Band 5	Band 6	Band 7	Band 8
Port 1	X	X	X	X	X	X	X	
Port 2								X

General Data

Indicated VSWR values are valid for a metallic ground plane of 0.5 x 0.5m or larger. Indicated gain values will be achieved on a metallic ground plane of 1 x 1 m or larger.

Electrical Data LNA

LNA noise figure dB	1.6
LNA current consumption (mA)	20
LNA is connected to	Port 2

SENCITY® Rail Antenna 1399.99.0026

MTBF (h) 3000000

This Antenna is compliant with the Radio Equipment Directive 2014/53/EU

EMC: EN50121-3-2 (2016)

ETSI EN 303 413 V.1.1.1 (2017-06)

ETSI EN 301 489-1 V2.2.3 (2019-03)

ETSI EN 301 489-19 V2.1.1 (2019-04)

LNA input voltage range: 3...5V

Total gain @90° elevation: 30 dBiC

Values for LNA power consumption, noise figure and gain are given for a 5V operating voltage and may differ slightly for a lower voltage.

Antennas with production date prior to 01-Oct-2020 support only GPS bands between 1574.397 - 1576.443 MHz.

Mechanical Data

Dimensions (mm) 154 x 100 x 256 (Height x Width x Depth)
Weight (kg) 1.6

High-voltage-protection: no voltage on RF port, if the catenary line touches antenna (EN 50124-1, 27.5 kVAC/1min).

High-current-protection: Designed acc. to UIC 533, DC-grounded antenna element protection against lightning and short circuit with catenary lines (EN50388, EN 50122-1, 40kA/0.1sec)

Corrosion: Low corrosion design according to MIL-F-14072(E), 96 hours Salt Spray test.

Mounting: Shall be installed in longitudinal position to the wind/driving direction.

Suitable for installation on high speed trains with a maximum speed of 500 km/hr.

Environmental Data

Environmental conditions indoor/outdoor
Operation temperature (°C) -55 to 85
Storage temperature (°C) -55 to 85
Transport temperature (°C) -55 to 85
IP rating IP67, IP69
Flammability rating EN 45545-2 R24 HL3
Solar radiation UL 746C, F1
2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant acc. Annex III
Lead-free soldered yes
WEEE 2012/19/EU no special marking needed
ELV 2000/53/EC compliant
REACH 1907/2006/EC compliant

Environmental tests: EN 50155:2018-05

Flammability rating: EN45545-2:2013 + A1:2015, NFPA-130:2017

Tested according to ISO 4589-2:2017, NFX 70-100-1:2006, ISO 5659-2:2011.

Antennas with production date prior to 01-Oct-2020 do not have NFPA-130 compliance.

Material Data

Radome colour RAL 7043 (dark grey)
Radome material ASA (acrylic ester-styrene-acrylonitrile)
Back plate/base plate colour grey
Back plate/base plate material Aluminium
Plating Passivated (Plating)

Related Products

9091.99.0235 Sencity Rail antenna grounding kit

9091.99.0236 Sencity Rail antenna conduit support Kit

9091.99.0261 Sencity Rail antenna mounting plate

9091.99.0252 Sencity Rail antenna adaptor plate

Related Documents

Mounting instruction DOC-0000295392
Painting instruction DOC-0000256180
Security instruction DOC-0000278984
Outline drawing DOU-00135091
Outline drawing 2 DOU-00154160
3D-model DOC-0000339670
CE compliancy DOC-0000896952

SENCITY® Rail Antenna 1399.99.0026

Additional Information

This product meets the Deutsche Bahn specifications for rolling stock equipment. Protected by Patents: US7327320B2, CN1765030B, AU2003218856A1, CA2521771C, SG114406, ZA200508290.