Ethernet Cable Cat6







Specifications


Connector to Connector : RJ45 Plug to RJ45 Plug

LAN Category : Cat6
Jacket Colour : Beige

Cable Type : UTP Flat Cable

Insulation Resistance : DC 300V/10ms, $10M\Omega$ (Min.)

Diagram



No.	Description	Qty.	Unit
1	Cat6 UTP 32AWG(7/0.08BC)×4P(ID:0.5mm) OD:1.9×6.2mm PT:421C PVC Mark: UTP CAT6 32AWG×4P	"L"	m
2	UTP CAT6 8P8C Transparent Crystal head square hole short body gold-plated terminal	2	Pcs
3	60P PVC PT:421C	10	g
4	CAT6 8P8C folding T set	2	Pcs

Part Number Table

Description	L ± T(mm)	Part Number
Ethernet Cable, Cat6, UTP Flat Cable, RJ45 Plug to RJ45 Plug, Beige	300±20	MP008329
	500±20	MP008330
	1000±20	MP008331
	1500±30	MP008332
	2000±30	MP008333
	3000±40	MP008334

Dimensions : Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

