



LL-NFM-KIT-DE-D

Low ESL LL series/NFM series

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Remarks	Qty
1	LLL153C70G474ME17	0510M/0204	X7S	4Vdc	0.47 μ F	\pm 20%	0.35max		20
2	LLL153C80G105ME21	0510M/0204	X6S	4Vdc	1 μ F	\pm 20%	0.35max		20
3	LLL1U4R60G435ME22	0610M/02404	X5R	4Vdc	4.3 μ F	\pm 20%	0.45max		20
4	LLL03TR61E223KE01	0306M/0102	X5R	25Vdc	0.022 μ F	\pm 10%	0.2max		20
5	NFM15PC435R0G3	1005M/0402	-	4Vdc	4.3 μ F	\pm 20%	0.5max		20
6	NFM15PC755R0G3	1005M/0402	-	4Vdc	7.5 μ F	\pm 20%	0.65max		20
7	NFM15PC915R0G3	1005M/0402	-	4Vdc	9.1 μ F	\pm 20%	0.7max		20
8	NFMJMPC156R0G3	1209M/05035	-	4Vdc	15 μ F	\pm 20%	0.65max		20
9	NFMJMPC226R0G3	1209M/05035	-	4Vdc	22 μ F	\pm 20%	0.8max		20
10	NFMJMPL226R0G5	1209M/05035	-	4Vdc	22 μ F	\pm 20%	0.65max		20