



Tie Harness Mounts are designed to be attached to the wire harness during assembly with 2 cable ties. Ties can be installed by hand or more efficiently with *PANDUIT* Automatic Cable Tie Tooling. Use with Harness Board Standoff Posts. Available with or without corrugated tubing location tab.

Part Number:	THMSP20F-C30
Product Family:	Tie Harness Mounts
Product Line:	Push/Tree Barb
RoHS Compliancy Status:	Compliant
Part Description:	Harness Cable Tie Mount
Product Type:	Cable Tie Mounts - Tie Harness Mount
Material:	Heat Stabilized Nylon 6.6
Color:	Black
UL Recognized:	E136577
Height (In.):	.47
Height (mm):	16.5
Length (In.):	1.54
Length (mm):	39.1
Width (In.):	.37
Width (mm):	9.4
Corrugated Tubing Tab:	No
Environment:	Indoors/High Temp
Flammability Rating:	UL94 V-2
Max. Panel Thickness (In.):	.160
Max. Panel Thickness (mm):	4.1
Mounting Method:	Push Barb

