

Product data sheet

Specifications



Harmony XVU, Illuminated LED unit for modular tower lights, orange, Ø60, high flashing, IP65, 24 V AC/DC

XVUC65

Main

Range of product	Harmony XVU
Product or component type	Modular tower light
Beacon or indicator bank unit type	LED unit
Mounting diameter	60 mm
Component name	XVU
Light source	LED, orange
Device application	Automotive Packaging machine Machine tools

Complementary

Signalling type	High flashing
Assembly style	Customer assembly, up to 3 units
Material	PC (polycarbonate) V-2 conforming to UL 94
[Us] rated supply voltage	24 V AC/DC
Maximum power dissipation in W	2.9 W
Current consumption	<= 150 mA
Signalling type	High flashing
Length	60 mm
Net weight	0.085 kg

Environment

Product certifications	UL CSA CE EAC RCM
Ambient air temperature for storage	-40...70 °C
IP degree of protection	IP65
Ambient air temperature for operation	-25...50 °C
Vibration resistance	2 gn

Packing Units

Package 1 Weight	77.450 g
Package 1 Height	9.050 cm
Package 1 width	9.050 cm
Package 1 Length	13.400 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Illuminated LED Unit

Dimensions

