

28 mm Sleeved Quick Drill



SPECIFICATION

Product Name	28 mm Sleeved Quick Drill
Item Code	SRSDQ28
Dimensions	Drill Bit - 28 mm x 540 mm Sleeve - Inside Diameter 22.5 mm - Sleeve Length 345 mm

ABOUT

Drill bit and sleeve technology that simplifies passing of cable or pipe through cavity walls; suitable for walls up to 345 mm deep.

- UK Gas regulation compliant Speci ically designed for gas engineers, meets all current legislation
- Secure Installation sleeve compacts and locks on entry to create a clear passage for service installs
- Reduced installation time integrated system allows single operation drill and sleeve insertion, enabling pipework and multiple cables to be installed within seconds
- Differentiated hole size yellow sleeve design identi ies gas pipes
- Multi-purpose high Performance 28 mm carbide drill bit speci ically designed for use with Thru-in-1 but also operates as standard drill bit
- Compatible with standard cordless drills increasing the
- number of holes per battery charge.
- Long tool life carbide grade tip ensures maximum life span
- Clean & accurate drill truer, rounder holes in multiple material types.
- Proven flute and tip geometries enable maximum spoil removal.
- Optimum tip support copper brazed
- Increased penetration and efficiency latest carbide tip technology
- · Atmosphere controlled hardening, tempering and brazing
- Strength & durability manufactured with high quality steel
- Secure & stable sleeve installation unique top hat guide secures the sleeve during drilling

APPLICATION

- Drill hole
- Cut over sized copper pipe for sleeve
- Insert copper pipe through wall
- Inspect both sides of wall to make sure sleeve is flush

CONTENTS

- 1 x 28 mm Sleeved Quick Drill
- 1 x Sleeve