

ILD LFR45D037



Ideal for new builds - Only a 45mm cut-out (for MR11 12V GU4 or MR11 240V GU10 lamps). Great for tight spaces - 38.5mm super-low profile. Aesthetic - Ultra-thin 1mm blend-in bezel with a premium finish. Easy wiring - with a Fast-Fit, loop-in/loop-out, junction box for tool free assembly. Easy to install and remove - Durable steel assembly. Extended lamp life - Open design allows airflow to extend lamp life compared to traditional designs. 45mm Cut-Out, 64mm Diameter, IP65. This downlight is fire rated to 30, 60 and 90 minutes in compliance with BS476 Part 21:1987, Air Tightness compliant with Part C and Part L and Resistance to Sound compliant with Part E. See installation guide for full details.

Details

| | |
|-----------------------------|---------------------------------------|
| Barcode: | 5055788254553 |
| Category: | Downlights |
| Range Name: | Evofire mini |
| Product Body Finish: | Matt white |
| Market Segment: | Commercial indoor, Residential indoor |
| Finish: | Matt White |
| Warranty (Years): | 3 |
| CE RoHS: | Yes |

Physical Data

| | |
|---------------------------------|--------------------------|
| Product Depth (mm): | 38.5 |
| Product Weight (g): | 10 |
| Material: | Steel, Glass |
| Overall diameter (mm): | 64 |
| Construction: | Pressed Steel, Glass |
| Cut Out Diameter (mm): | 45 |
| Luminaire Fixing: | Recess mounted |
| Placement / Application: | Indoor, General Lighting |

Electrical Data

Light Data

| | |
|----------------------------|------------|
| Fire Rating (mins): | 30, 60, 90 |
|----------------------------|------------|

Environment

| | |
|-----------------|-----|
| CE RoHS: | Yes |
|-----------------|-----|

| | |
|---------------------------------|------|
| IP Rating (Back/Recessed side): | IP20 |
| IP Rating (Ingress Protection): | IP65 |

Packaging

| | |
|----------------------|------|
| Package Weight (g): | 13 |
| Package Length (mm): | 70 |
| Package Width (mm): | 70 |
| Package Depth (mm): | 65 |
| Qty per euro pallet: | 1632 |