

ILD LFR70D029



The Evofire Fire Rated Downlight is a safe and attractive fitting for a GU10 or MR16 LED lamp. The fully open design of the Evofire does not conceal your lamp in a large metal canister, which can trap some of the heat it generates, lowering lamp lifetime and performance. Lamps installed in an Evofire run at up to 10 degrees C cooler than a typical can-style fire rated downlight from leading LED brands - this can extend the lifetime of your lamps. As well being very tough thanks to its steel construction, The Evofire is also a highly aesthetic choice for Fire Rated lighting. The 1mm blend-in bezel is up to 10 times thinner than typical IP65 rated downlights, has a high quality powder coating and fits almost flush with your ceiling, so the downlight looks discreet and pleasing in any setting. Featuring a built-in Insulation Guard which allows loft insulation to be safely laid on top of the downlight, while maintaining air-flow around the lamp. This downlight is fire rated to 30, 60 and 90 minutes in compliance with BS476 Part 21:1987, Air Tightness compliant with Part C and Part L and Resistance to Sound compliant with Part E. See installation guide for full details.

Details

Barcode:	5055788253815
Category:	Downlights
Range Name:	Evofire
Product Body Finish:	Black
Market Segment:	Commercial indoor, Residential indoor
Features:	With Insulation Guard
Warranty (Years):	3
CE RoHS:	Yes

Physical Data

Product Depth (mm):	83
Product Weight (g):	173
Material:	Steel, Glass
Overall diameter (mm):	85
Construction:	Pressed Steel, Glass
Cut Out Diameter (mm):	70
Bulb or Luminaire Shape:	Round
Luminaire Fixing:	Recess mounted
Placement / Application:	Indoor, General Lighting

Electrical Data

Light Data

Fire Rating (mins): 30, 60, 90

Environment

CE RoHS: Yes

IP Rating (Back/Recessed side): 20

IP Rating (Ingress Protection): IP65

Packaging

Package Weight (g): 188

Package Length (mm): 90

Package Width (mm): 90

Package Depth (mm): 115

Qty per euro pallet: 1360