

Product data sheet

Specifications



Harmony, Solid state relay pre assembled, 0.1 A, DC switching, screw sockets, input 4...12 V DC, output 1...48 V DC

SSL1D101JDPV

Main

Range of product	Harmony Solid State Relays
Product or component type	Solid state relay up to 10 A
Device short name	SSL
Network number of phases	1 phase
Output switching mode	DC switching

Complementary

Mounting support	Screw socket
[In] rated current	0.1 A
Output voltage	1...48 V DC
CLAMPING FORCE	< 0.5 N.m 4.4 lb-in
Connections - terminals	Flexible cable with cable end,clamping capacity: 0.2...2.5 mm² (AWG 24...AWG 14) Solid cable with cable end,clamping capacity: 0.2...2.5 mm² (AWG 24...AWG 14)
Capacitance unbalance	1.5 pF input/output
Minimum switching voltage	4 V DC turn-on
Maximum switching voltage	1 V DC turn-off
Input impedance	833 Ohm
Solid state output type	Transistor output DC switching
Load current	0.001...0.1 A
Tansient Overvoltage	60 V DC
Surge current	0.3 A for 10 ms
Maximum voltage drop	<1 V on-state
Maximum leakage current	0.001 mA off-state
Response time	0.12 ms (turn-off) 0.1 ms (turn-on)
Overvoltage category	III
Width	6.2 mm
Height	96.5 mm
Depth	79.5 mm

Net weight	0.0285 kg
------------	-----------

Environment

Flame retardance	V0 conforming to UL 94
Dielectric strength	2500 V for input/output
Pollution degree	2
Standards	IEC 60950-1 IEC 61000 IEC 62314 IEC 61984 EN 61984
Product certifications	UL CSA CE UL 508 CSA22.2 No. 14-10 GOST
Marking	CURus CSA CE EAC
IP degree of protection	IP20
Ambient air temperature for operation	-20...70 °C
Ambient air temperature for storage	-20...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	33 g
Package 1 Height	9.65 cm
Package 1 width	0.625 cm
Package 1 Length	7.9 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	30
Package 2 Weight	1.04 kg
Package 2 Height	9 cm
Package 2 width	10 cm
Package 2 Length	20 cm
Unit Type of Package 3	S03
Number of Units in Package 3	60
Package 3 Weight	2.754 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability


Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Contractual warranty

Warranty	18 Months
----------	-----------

Dimensions



Derating Curves



A : Load Current (Amperes)

B : Ambient Temperature (°C)