

19" Locking Rack Drawer - 2U Short



Description

Shallow depth, 19" steel rack drawer with integrated lock and ball race drawer slides for installation into 19" rack cabinets or mobile flight cases.


Features

- 19" Rack mount drawer
- Sprung drawer release catch
- Integrated lock supplied with 2 keys
- Ball race drawer slides
- Release catch in drawer slides for easy removal
- Steel construction with a black powder coating

Specifications

Rack U Height	: 2U
For Use With	: 19" Rack Cabinets
Internal Drawer Dimensions	: 398mm×62mm×198mm (W×H×D)
External Dimensions	: 482mm×89mm×210mm (W×H×D)
Weight	: 3.7kg

Diagram



Part Number Table

Description	Part Number
19" Locking Rack Drawer - 2U Short	RD2S

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. PULSE is the registered trademark of Premier Farnell Limited 2019.

Newark.com/b/Pulse
Farnell.com/b/Pulse
sg.element14.com/b/pulse

