

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0011030043](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Extraction Tool for Micro-Fit Terminals

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|--------------------------------|---|
| Product Family | Application Tooling |
| Series | 207121 |
| Function | Extraction |
| Geographic Area | Global |
| Level of Automation | Manual |
| More Detailed Tech Information | applicationtooling@molex.com |
| Overview | Application Tooling |
| Product Name | N/A |
| Tool Type | Extraction Hand Tool |
| UPC | 800754211260 |
| Warranty Disclaimer | CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified. |

Material Info

Engineering Number HT60923A

Reference - Drawing Numbers

Application Tooling Documents
ATS-011030043-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



EU ELV

Not Relevant

EU RoHS

Missing Compliance Data

REACH SVHC

Missing Compliance Data

Halogen-Free Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[207121](#) Series

Application Tooling

Description

FAQ

Product #

| | |
|---|----------------------------|
| Micro-Fit High-Current RMF Crimp Terminal, Female, 2.540µm Bright Tin Plating, 18 AWG | 2039510001 |
| Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 26-30 AWG | 2064600011 |
| Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 26-30 AWG | 2064600012 |
| Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 26-30 AWG | 2064600013 |
| Micro-Fit+ Crimp Terminal, Female, | 2064600021 |

| | |
|--|-------------------|
| Tin (Sn) Plating, 20-24 AWG Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 20-24 AWG | <u>2064600022</u> |
| Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 20-24 AWG | <u>2064600023</u> |
| Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 18 AWG | <u>2064600031</u> |
| Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 18 AWG | <u>2064600032</u> |
| Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 18 AWG | <u>2064600033</u> |
| Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 16 AWG | <u>2064600041</u> |
| Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 16 AWG | <u>2064600042</u> |
| Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 16 AWG | <u>2064600043</u> |
| Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 20-24 AWG, Reel | <u>430300001</u> |
| Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel | <u>430300002</u> |
| Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel | <u>430300003</u> |
| Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 26-30 AWG, Reel | <u>430300004</u> |
| Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Reel | <u>430300005</u> |

Micro-Fit 3.0 Crimp 430300006
Terminal, Female,
with Select Gold (Au)
Plated Phosphor
Bronze Contact,
26-30 AWG, Reel

Micro-Fit 3.0 Crimp 430300007
Terminal, Female,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Bag

Micro-Fit 3.0 Crimp 430300008
Terminal, Female,
with Select Gold (Au)
Plated Phosphor
Bronze Contact,
20-24 AWG, Bag

Micro-Fit 3.0 Crimp 430300009
Terminal, Female,
with Select Gold (Au)
Plated Phosphor
Bronze Contact,
20-24 AWG, Bag

Micro-Fit 3.0 Crimp 430300010
Terminal, Female,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Bag

Micro-Fit 3.0 Crimp 430300011
Terminal, Female,
with Select Gold (Au)
Plated Phosphor
Bronze Contact,
26-30 AWG, Bag

Micro-Fit 3.0 Crimp 430300012
Terminal, Female,
with Select Gold (Au)
Plated Phosphor
Bronze Contact,
26-30 AWG, Bag

Micro-Fit 3.0 Crimp 430300038
Terminal, Female,
with Tin (Sn)
Plated Phosphor
Bronze Contact,
18 AWG, .073in /
1.85mm Max
Insulation Outside
Diameter, Reel

Micro-Fit 3.0 430300039
Crimp Terminal,
Female, with 0.38 μ m
Select Gold (Au)
Plated Phosphor
Bronze Contact,
18 AWG, .073in /
1.85mm Max
Insulation Outside
Diameter, Reel

Micro-Fit 3.0 430300040
Crimp Terminal,
Female, with 0.76 μ m
Select Gold (Au)

Plated Phosphor
Bronze Contact,
18 AWG, .073in /
1.85mm Max
Insulation Outside
Diameter, Reel
Micro-Fit 3.0 Crimp [430310001](#)
Terminal, Male,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit 3.0 Crimp [430310002](#)
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit 3.0 Crimp [430310003](#)
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit 3.0 Crimp [430310004](#)
Terminal, Male,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel
Micro-Fit 3.0 Crimp [430310005](#)
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel
Micro-Fit 3.0 Crimp [430310006](#)
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel
Micro-Fit 3.0 Crimp [430310007](#)
Terminal, Male,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Bag
Micro-Fit 3.0 Crimp [430310008](#)
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Bag
Micro-Fit 3.0 Crimp [430310009](#)
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze

Contact, 20-24 AWG,
Bag

Micro-Fit 3.0 Crimp 430310010

Terminal, Male,
with Tin (Sn) Plated
Phosphor Bronze

Contact, 26-30 AWG,
Bag

Micro-Fit 3.0 Crimp 430310011

Terminal, Male,
with 0.38µm Select
Gold (Au) Plated

Phosphor Bronze

Contact, 26-30 AWG,
Bag

Micro-Fit 3.0 Crimp 430310012

Terminal, Male,
with 0.76µm Select
Gold (Au) Plated

Phosphor Bronze

Contact, 26-30 AWG,
Bag

Micro-Fit 3.0 Crimp 430310021

Terminal, Male,
with Tin (Sn)

Plated Phosphor

Bronze Contact,

18 AWG, .073in /

1.85mm Max

Insulation Outside

Diameter, Reel

Micro-Fit 3.0 430310022

Crimp Terminal,

Male, with 0.38µm

Select Gold (Au)

Plated Phosphor

Bronze Contact,

18 AWG, .073in /

1.85mm Max

Insulation Outside

Diameter, Reel

Micro-Fit 3.0 430310023

Crimp Terminal,

Male, with 0.76µm

Select Gold (Au)

Plated Phosphor

Bronze Contact,

18 AWG, .073in /

1.85mm Max

Insulation Outside

Diameter, Reel

Micro-Fit TPA Crimp 430315003

Terminal, Male, with

Tin (Sn) Pre-plated

Phosphor Bronze

Contact, 20-24 AWG,

Reel

Micro-Fit TPA Crimp 430315004

Terminal, Male,

with 0.38µm Select

Gold (Au) Plated

Phosphor Bronze

Contact, 20-24 AWG,

Reel

Micro-Fit TPA Crimp [430315005](#)
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel

Micro-Fit TPA Crimp [430315006](#)
Terminal, Male, with
2.54µm Matte Tin
Plated Phosphor
Bronze Contact,
20-24 AWG, Reel

Micro-Fit TPA Crimp [430315007](#)
Terminal, Male, with
Tin (Sn) Pre-plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel

Micro-Fit TPA Crimp [430315008](#)
Terminal, Male,
with 0.38µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel

Micro-Fit TPA Crimp [430315009](#)
Terminal, Male,
with 0.76µm Select
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel

Micro-Fit TPA Crimp [430315010](#)
Terminal, Male, with
2.54µm Matte Tin
Plated Phosphor
Bronze Contact,
26-30 AWG, Reel

Micro-Fit 3.0 Crimp [457730001](#)
Terminal, Female,
with Lubricant, with
Tin (Sn) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel

Micro-Fit 3.0 Crimp [457730003](#)
Terminal, Female,
with Lubricant, with
Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel

Micro-Fit 3.0 Crimp [457730006](#)
Terminal, Female,
with Lubricant, with
Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel

Micro-Fit 3.0 Crimp [457730053](#)
Terminal, Female,
with Lubricant, with
Gold (Au) Plated
Phosphor Bronze

Contact, 20-24 AWG,
Reel

Micro-Fit RMF 462350001

Reduced Mating
Force, Crimp
Terminal, Female,
with 0.38 μ m

Selective Gold (Au)
over Nickel (Ni),
20-24 AWG, without
Lubricant

Micro-Fit RMF 462350002

Reduced Mating
Force, Crimp
Terminal, Female,
with 0.76 μ m

Selective Gold (Au)
over Nickel (Ni),
20-24 AWG, without
Lubricant

Micro-Fit RMF 462350003

Reduced Mating
Force, Crimp
Terminal, Female,
with 0.38 μ m

Selective Gold (Au)
over Nickel (Ni),
26-30 AWG, without
Lubricant

Micro-Fit RMF 462350004

Reduced Mating
Force, Crimp
Terminal, Female,
with .0.76 μ m

Selective Gold (Au)
over Nickel (Ni),
26-30 AWG, without
Lubricant

Micro-Fit RMF 462355001

High Mating
Cycle, Reduced
Mating Force,
Crimp Terminal,
Female, with 0.38 μ m

Selective Gold (Au)
over Nickel (Ni),
20-24 AWG, with
Lubricant

Micro-Fit RMF 462355002

High Mating
Cycle, Reduced
Mating Force,
Crimp Terminal,
Female, with 0.76 μ m

Selective Gold (Au)
over Nickel (Ni),
20-24 AWG, with
Lubricant

Micro-Fit RMF 462355003

High Mating
Cycle, Reduced
Mating Force,
Crimp Terminal,
Female, with 0.38 μ m

Selective Gold (Au)

| | |
|---|------------------|
| over Nickel (Ni), 26-30 AWG, with Lubricant Micro-Fit RMF High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with .0.76µm Selective Gold (Au) over Nickel (Ni), 26-30 AWG, with Lubricant | <u>462355004</u> |
| 1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 28-32 AWG, Reel | <u>500588000</u> |
| 1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 28-32 AWG, Bag | <u>500588100</u> |
| 1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 26-28 AWG, Reel | <u>500798000</u> |
| 1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 26-28 AWG, Bag | <u>500798100</u> |
| 1.25mm Pitch, PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 26-28 AWG, Reel | <u>501258000</u> |
| 1.25mm Pitch, PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 26-28 AWG, Bag | <u>501258100</u> |
| 1.25mm Pitch, PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 28-32 AWG, Reel | <u>501338000</u> |
| 1.25mm Pitch, PicoBlade Male Crimp Terminal, Tin (Sn) Plating, 28-32 AWG, Bag | <u>501338100</u> |
| 2.00mm Pitch, Micro- Latch Female Crimp Terminal, Tin (Sn) Plating, 24-30 AWG, Reel | <u>502128000</u> |
| 2.00mm Pitch, Micro- Latch Female Crimp Terminal, Tin (Sn) Plating, 24-30 AWG, Bag | <u>502128100</u> |
| 2.00mm Pitch, Micro- Latch Female Crimp | <u>503728000</u> |

Terminal, Tin (Sn)
Plating, 22-26 AWG,
Reel
2.00mm Pitch, Micro-503728100
Latch Female Crimp
Terminal, Tin (Sn)
Plating, 22-26 AWG,
Bag
OBD-II Crimp 504208000
Terminal, Female,
50420, 4.00mm Pitch
DuraClik Crimp 5600850101
Terminal, Female,
22-26 AWG, Reel

This document was generated on 11/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION