

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638190000

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for Micro-Fit 3.0 Terminals, 20-30 AWG

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

See Tooling Specification (PDF) Above. Type: 4D Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Hand Crimp Tool

800756936826

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

332.600/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638190000-001, TM-638000029-001, TM-638000029CN-001, TM-638000029SP-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	430300001
Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	430300002
Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor	430300003

Bronze Contact,
20-24 AWG, Reel
Micro-Fit 3.0 Crimp [430300004](#)
Terminal, Female,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel
Micro-Fit 3.0 Crimp [430300005](#)
Terminal, Female,
with Select Gold (Au)
Plated Phosphor
Bronze Contact,
26-30 AWG, Reel
Micro-Fit 3.0 Crimp [430300006](#)
Terminal, Female,
with Select Gold (Au)
Plated Phosphor
Bronze Contact,
26-30 AWG, Reel
Micro-Fit 3.0 Crimp [430300007](#)
Terminal, Female,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Bag
Micro-Fit 3.0 Crimp [430300008](#)
Terminal, Female,
with Select Gold (Au)
Plated Phosphor
Bronze Contact,
20-24 AWG, Bag
Micro-Fit 3.0 Crimp [430300009](#)
Terminal, Female,
with Select Gold (Au)
Plated Phosphor
Bronze Contact,
20-24 AWG, Bag
Micro-Fit 3.0 Crimp [430300010](#)
Terminal, Female,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Bag
Micro-Fit 3.0 Crimp [430300011](#)
Terminal, Female,
with Select Gold (Au)
Plated Phosphor
Bronze Contact,
26-30 AWG, Bag
Micro-Fit 3.0 Crimp [430300012](#)
Terminal, Female,
with Select Gold (Au)
Plated Phosphor
Bronze Contact,
26-30 AWG, Bag
Micro-Fit 3.0 Crimp [430310001](#)
Terminal, Male,
with Tin (Sn) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel
Micro-Fit 3.0 Crimp [430310002](#)
Terminal, Male,
with 0.38μm Select

Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel

Micro-Fit 3.0 Crimp [430310003](#)

Terminal, Male,
with 0.76µm Select

Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Reel

Micro-Fit 3.0 Crimp [430310004](#)

Terminal, Male,
with Tin (Sn) Plated

Phosphor Bronze
Contact, 26-30 AWG,
Reel

Micro-Fit 3.0 Crimp [430310005](#)

Terminal, Male,
with 0.38µm Select

Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel

Micro-Fit 3.0 Crimp [430310006](#)

Terminal, Male,
with 0.76µm Select

Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Reel

Micro-Fit 3.0 Crimp [430310007](#)

Terminal, Male,
with Tin (Sn) Plated

Phosphor Bronze
Contact, 20-24 AWG,
Bag

Micro-Fit 3.0 Crimp [430310008](#)

Terminal, Male,
with 0.38µm Select

Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Bag

Micro-Fit 3.0 Crimp [430310009](#)

Terminal, Male,
with 0.76µm Select

Gold (Au) Plated
Phosphor Bronze
Contact, 20-24 AWG,
Bag

Micro-Fit 3.0 Crimp [430310010](#)

Terminal, Male,
with Tin (Sn) Plated

Phosphor Bronze
Contact, 26-30 AWG,
Bag

Micro-Fit 3.0 Crimp [430310011](#)

Terminal, Male,
with 0.38µm Select

Gold (Au) Plated
Phosphor Bronze
Contact, 26-30 AWG,
Bag

Micro-Fit 3.0 Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Bag	<u>430310012</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Lubricant, with Tin (Sn) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	<u>457730001</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Lubricant, with Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	<u>457730003</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Lubricant, with Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Reel	<u>457730006</u>
Micro-Fit 3.0 Crimp Terminal, Female, with Lubricant, with Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel	<u>457730053</u>