





Rotary Hammer

TC-RH 620 4F

Item No.: 4257990

Ident No.: 21010

Bar Code: 4006825654592

The TC-RH 620 4F impact drill is the perfect entry-level model and has 4 functions: drilling, impact drilling, chiseling with/without chisel lock. It combines performance with compact design. Its low weight and ergonomic handle with soft grip make it ideal to work with - incl. overhead. The pulse generator for all the functions is the position switch, while the pneumatic impact mechanism provides good forward traction. A continuous operation lock ensures user-friendly operation, the robust SDS-plus tool chuck has a semi-automatic function, electronic speed control ensures that the tool can be adjusted to the particular material & application and the solid metal drilling depth stop can be adjusted to any depth. Supplied in the E-Box Basic.

Features & Benefits

- 4 func.: Drilling/impact drilling/chiseling with and without lock
- One position switch for all functions
- The entry-level model performance combined with compact design
- Continuous operation lock for comfortable operation
- Low in weight for flexible operation even overhead
- Pneumatic impact mechanism for very good forward traction
- Robust SDS-plus tool chuck with semi-automatic function
- Speed electronics for adjusting the tool to material&application
- Ergonomic handle with soft grip
- Infinitely adjustable drilling depth stop made of solid metal
- Supplied in an E-Box Basic transport and storage case

Technical Data

230-240 V | 50 Hz - Mains supply - Power 620 W - Idle speed 1250 min^-1 5200 min^-1 - Impact rate - Impact power 2.2 JSDS-plus - Tool holder - Drilling capacity in concrete 20 mm

Logistic Data

- Product weight 2.63 kg - Gross weight single packaging 4.15 kg

417 x 113 x 358 mm - Dimensions single packaging

- Pieces per export carton 4 Pieces - Gross weight export carton 17.5 kg

- Dimensions export carton 385 x 465 x 435 mm - Container quantity (20"/40"/40"HC) 1380 | 2800 | 3300















