PHILIPS Lighting



MASTER Value GLASS LED bulbs

MASTERVLELEDBulb D5.9-60W E27 927A60FR G UK

Featuring a classic heritage design, classic filament LED lamps combine the familiar shapes of incandescent bulbs with the benefits of the long-lasting LED technology. The product offers more energy saving compared with normal LED bulbs, and also provides the customer with a good light experience and superior dimming performance. MASTER Value Glass Led Bulbs deliver significant energy savings, offering 30% more compared to normal LEDs. They provide excellent quality of light. By offering a lifetime of 15,000 hours, they reduce maintenance costs.

Product data

General Information		
Cap base	E27 [E27]	
EU RoHS compliant	Yes	
Nominal lifetime (nom.)	15000 h	
Switching cycle	20,000X	
Light Technical		
Colour Code	927 [CCT of 2,700 K]	
Luminous flux (nom.)	806 lm	
Colour designation	Warm white (WW)	
Correlated Colour Temperature (Nom)	2700 K	
Luminous efficacy (rated) (nom.)	136.00 lm/W	
Colour consistency	<6	
Colour rendering index (nom.)	90	
LLMF at end of nominal lifetime (nom.) 70 %		


Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	5.9 W
Lamp current (nom.)	35 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	Yes
-	

MASTER Value GLASS LED bulbs

Mechanical and Housing	
Lamp Finish	Frosted
Bulb shape	A60 [A 60mm]
Approval and Application	
Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	6 kWh
	574362
Product Data	
Full product code	871951434786101

Order product name	MASTERVLELEDBulb D5.9-60W E27 927A60FR
	G UK
EAN/UPC – product	8719514347861
Order code	34786101
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929003057799
SAP net weight (piece)	0.030 kg

Dimensional drawing




MASTERVLELEDBulb D5.9-60W E27 927A60FR G UK 60 mm 104 mm	Product	D	с
	MASTERVLELEDBulb D5.9-60W E27 927A60FR G UK	60 mm	104 mm

Bulb A60 60W 806lm 2700K E27 D FR

Photometric data

	1 x 9290030577 5.9W
	t a Kild in
University of the second secon	




LEDbulb MAS 5,9W A60 E27 927 FR-GUL

LEDbulb MAS A60 5,9W E27 927 FR-LDD


MASTER Value GLASS LED bulbs

Photometric data



LEDbulb MAS 5,9W A60 E27 927 FR-POC

Lifetime



15K LED

15K LMP



© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.