



CorePro GLASS LED candles and lusters



CorePro LEDCandleND2-25W ST35 E14 827CLG

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lusters, as comparing with convential lamps, it provide 90% energy saving. CorePro Glass LED candles and lusters provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Product data

General Information		
Cap-Base	E14 [E14]	
EU RoHS compliant	Yes	
Nominal Lifetime (Nom)	15000 h	
Switching Cycle	20000X	
Technical Type	2-25W	
Flux measurement reference	Sphere	
Light Technical		
Color Code	827 [CCT of 2700K]	
Luminous Flux (Nom)	250 lm	
Color Designation	Warm White (WW)	
Correlated Color Temperature (Nom)	2700 K	
Luminous Efficacy (rated) (Nom)	125.00 lm/W	
Color Consistency	<6	
Color Rendering Index (Nom)	80	
LLMF At End Of Nominal Lifetime (Nom) 70 %		

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	2 W
Lamp Current (Nom)	20 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	36 ℃
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

Datasheet, 2021, November 12 data subject to change

CorePro GLASS LED candles and lusters

Bulb Shape	ST35	
Approval and Application		
Energy Efficiency Class	Е	
Energy Saving Product	Yes	
Suitable For Accent Lighting	No	
Energy Consumption kWh/1000 h	2 kWh	
EPREL Registration Number	387362	
Product Data		
Full product code	871951434772400	

Order product name	CorePro LEDCandleND2-25W ST35 E14
	827CLG
EAN/UPC - Product	8719514347724
Order code	929001238592
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001238592
Net Weight (Piece)	0.014 kg


Dimensional drawing




Product	D	С
CorePro LEDCandleND2-25W ST35 E14 827CLG	35 mm	97 mm

filament 2.5W-25W 250lm NAD 2200K E14ND

Photometric data






LED Lamps, Lightcolour /827 ND CL

Classic LEDCandle ND 2-25W ST35 827 CL


CorePro GLASS LED candles and lusters


Photometric data



Classic LEDCandle ND 2-25W ST35 827 CL

Lifetime





15K LED 15K LMP



© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.