
HIGH-LEVERAGE CABLE CUTTERS

30% less force needed to cut*



 **MADE IN
USA**

**2/0
SOFT
COPPER**



**4/0
ALUMINUM**



**100-pair 24 AWG
COMMUNICATIONS
CABLE**



**KLEIN
TOOLS®**



*30% less force to cut compared to Klein's 63050 model

HIGH-LEVERAGE CABLE CUTTERS

Cable-gripping shear-type jaws and high-leverage design cut aluminum, copper and communications cable. Cutting surfaces are through-hardened, not case-hardened for added durability and long life. Available in two handle types. The Journeyman™ model, also, strips 1/0 and 2/0 cable.

CABLE-GRIPPING SHEAR-TYPE JAWS



HIGH-LEVERAGE DESIGN



INTEGRATED STRIPPING HOLE



30% less force needed to cut

63225

J63225N

- Cut 4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications cable
- High-leverage design for exceptional cutting capability
- Precision, one-hand shearing action
- Perfect for working in **confined spaces**
- **Through-hardened** (not case-hardened) for longer-lasting cutting surfaces
- **Hot-riveted joint** for smooth action & no handle wobble
- **Custom, US-made tool steel** for maximum durability

Unique to the J63225N

- **Integrated stripping hole** strips 1/0 and 2/0 cable
- **State-of-the-art, dual material Journeyman™ handles** provide a better grip without sacrificing tool strength or durability

2/0
SOFT COPPER



4/0
ALUMINUM



100-pair 24 AWG
COMMUNICATIONS CABLE



For Professionals
SINCE 1857™

Cat. No.	UPC 0-92644+	Cutting Capacity	Strips	Overall Length
63225	63225-9	4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications cable	—	9.07" (23 cm)
NEW J63225N	63227-3	4/0 aluminum, 2/0 soft copper, 100-pair 24 AWG communications cable	1/0 and 2/0 cable	9.3" (24 cm)

Warning statement: Do not use to cut steel or ACSR. Visit www.kleintools.com for safety warnings.
*30% less force to cut compared to Klein's 63050 model.



See our complete line of Cable Cutters
www.kleintools.com



© 2020 Klein Tools, Inc.
Lincolnshire, IL 60069
82922 Rev. 10/20 B