

PSS55D

UPC:782116199549

Dimensions:

- **Height:** 4 IN
- **Length:** 7.5 IN
- **Width:** 9 IN

Weight:3.05 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Convection cooling, finger-safe cover, short-circuit protection, auto restart
- **Wattage:** 55W
- **Operating Temperature - Max:** 50 C
- **Operating Temperature - Min:** -25 C
- **Enclosure:** IP20
- **Frequency Rating:** 47-63 Hz
- **Input Voltage:** 480-600V
- **Output Voltage:** 24V
- **Rated Operational Current:** 2.3A, 0.07A input, 15A inrush, 10A surge
- **Series:** PSS
- **Phase:** Three-phase

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - PSS55D](#)

Certifications:

- UL 508
- F47 Certified
- CSA Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.