

# In Ear Earphones with Digital Stereo Sound

pro-SIGNAL



## Specifications

Loudspeaker : Ø15mm  
Frequency Range : 20Hz to 20000Hz  
Sensitivity : 90 ±3dB  
Impedance : 32Ω  
Max. Power Input : 60mW  
Cable length : 1.2m

## Part Number Table

Description	Colour	Part Number
In Ear Earphones with Digital Stereo Sound	White	PSG08479
	White & Silver	PSG08480
	Black	PSG08481

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands  
Farnell.com/exclusive-brands  
Element14.com/exclusive-brands

pro-SIGNAL