

XN8P-2**3 YEAR Warranty** 

Part Number: Model: XN8P-2

Product Group: CCTV

Product Type: HD-IP NVR

**8MP (4K) 8 Channel H265 NVR**

IP Camera Channels	8 Channel
Compression	Audio: G.711a Video: H264/H265
Onvif	Yes
Maximum Recording Resolution	8MP (4K)
Recording Bandwidth	128Mbps
Live/Playback	8 Channel - 8MP (4K): 45fps, 8 Channel - 4MP: 90fps, 8 Channel - 2MP: 180fps
Video Output	1 x HDMI (4K), 1 x VGA
Mobile Viewer	XIQ Mobile CMS App (Android/iOS)
Display Split	1/4/6/8/9
Display Resolution	1024x768, 1280x720, 1280x1024, 1400x900, 1920x1080 2560x1440, 3840x2160
Recording Modes	Continuous/Manual/Motion Detection
Ethernet	RJ45 100/1000 Base-T
Internal Hard Drive	2x SATA HDD or 1x SATA HDD up to 10TB, plus NAS Storage

PoE Ports	8 Port
Alarm Input/Outputs	8 In/1 Out
Audio Output	1
RS485	Yes
USB Interface	2 (Front/Rear)
Power Supply	DC 48V/2A
Power Consumption	5W
Operating Temperature	0°C to +40°C
Dimensions (WHD)	380 x 50 x 340mm
Warranty	3 Year Warranty