

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731140389](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT Plastic Backshell with Male D-Sub Connector, Shielded, Shell Size 2, Straight Cable Outlet, IP67 Waterproof, Large Inner Chamber, with Locking Screws

Documents:

[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

General

Product Family	D-Sub Products
Series	173114
IP Rating	IP67
Overview	FCT D-Sub Connectors
Product Category	Backshell
Product Name	FCT Products
Type	IP67
UPC	191130516711

Physical

Cable Diameter	6.00-8.00mm
Material - Backshell	PC+ABS
Material - Screw	Brass
Material - Seal	Elastomer
Mounting Style	Locking Screw
Net Weight	25.000/g
Orientation	Straight
Packaging Type	Bag
Plating - Backshell	Nickel
Shield Type	Shielded Plastic
Shielded	Yes
Temperature Range - Operating	-25° to +70°C
Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67

Material Info

Engineering Number	FWH2A-15P-3649
--------------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[173114](#) Series