



14" Rechargeable Portable Digital TV

- 14.1" TFT LCD screen
- Resolution: 1280 x 800px
- Built-in re-chargeable lithium batteries
- Mains cable and 12-volt car charger adaptor provided
- 2.4GHz antenna

	EAN	5060750401866
Specifications	Model No.	C1420DVB Black
	Sales Market	UK
	Chipset	Mstar 3663
	Speaker Output	2 x 2w
	Actual Size of Display (diagonal)	14.1"
Display	Display Type	LED
	Resolution	1280 x 800
	Contrast ratio	300:1
	Brightness	200
Reception	TV System	ATV: PAL BG/DK/1 SECAM BG/DK/L/L, DTV:DVB-T & DVB-C & DVBT2, MPEG 2,MP@ML, MPEG 4
	TV Band	ATV 49MHz - 863MHz, DTV VHF (174MHz-- 230MHz), UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	Tuning System	FST
	Clock / Time Display	N/A
	Number of channels for storing	100 Analog / 400 Digital
Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Speaker Frequency range	150-20K Hz
	Speaker Distortion	<=7% Max
	Speaker Impedance	8ohm

Accessories	USER'S Manual	N/A
	Remote Control	YES x 1
	Car Cigarette Cable	YES x 1
	Adapter	YES x 1
	Adapter Cables	YES x 1
	Warranty	YES x 1
	Antenna	YES x 1
	Battery	1.5V(AAA)×2

Terminals	RF Antenna	1
	HDMI	YES x 1
	CVBS	YES x 1
	PC In	YES x 1(3.5 φ Mini Jack)
	Audio In	CVBS Audio x1
	Earphone Out	YES× 1
	USB on TV	YES× 1
	SD Slot	YES× 1

Features	APS	ATV, DVBT, DVBC storage in capture order
	OSD Language	English, Deutsch, Francais, Espanol, Portugese, Italian.
	EPG (Electronic Program Guide)	7 days
	Automatic Tuning	YES
	Sleep Timer	YES(240min)
	Color Temperature Adjustment	YES
	Picture Mode	Standard / Dynamic / Mild / User
	Home Mode	YES
	Hotel Mode	YES

Dimensions	Product size (mm)	330 x 33 x 223
	Weight (g)	880g