

HPE J9151A Compatible SFP+ Module - 10GBASE-LR - 10GbE Single Mode Fiber Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 10km - 1310nm - DDM HPE 2920, 2910a1, 3500yl

**Product ID:** J9151A-ST



The J9151A-ST is a HP J9151A compatible fiber transceiver module that has been designed, programmed and tested to work with HP brand switches and routers. It delivers dependable 10 GbE connectivity over fiber cable, for 10GBase-LR compliant networks, with a maximum distance of up to 10 km (6.2 mi).

Technical Specifications:

- Wavelength: 1310nm
- Maximum Data Transfer Rate: 10 Gbps
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- MTBF: 1,386,624,697 hours
- Power Consumption: < 1.3W
- Digital Diagnostics Monitoring (DDM): Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP+ modules and direct-attach SFP+ cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility

### Applications

### Features

- **100% HPE J9151A COMPATIBLE:** Works with HPE switches like 2920, 2910al, 3500yl, 3800, 5400zl and others
- **TECHNICAL SPECS:** 10GBASE-LR 10Gbps Single Mode (SMF) LC Connector 1310nm Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in HPE routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

---

#### Hardware

|                    |                         |
|--------------------|-------------------------|
| Warranty           | Lifetime                |
| Compatible Brand   | HPE                     |
| Industry Standards | IEEE 802.3ae 10GBASE-LR |

---

#### Performance

|                              |                     |
|------------------------------|---------------------|
| Maximum Data Transfer Rate   | 10.00 Gbps          |
| Max Transfer Distance        | 10 km (6.2 mi)      |
| Type                         | Single Mode         |
| Wavelength                   | 1310nm              |
| Fiber Operating Mode         | Full-Duplex         |
| DDM                          | Yes                 |
| Compatible Networks          | 10 Gbps             |
| MTBF                         | 1,386,624,697 hours |
| Power Consumption (In Watts) | < 1.3W              |



---

**Physical  
Characteristics**

|                   |                  |
|-------------------|------------------|
| Product Length    | 0.5 in [13.9 mm] |
| Product Width     | 2.3 in [58.4 mm] |
| Product Height    | 0.5 in [13.7 mm] |
| Weight of Product | 0.7 oz [21 g]    |

---

**Packaging  
Information**

|                              |                  |
|------------------------------|------------------|
| Package Length               | 4.5 in [11.5 cm] |
| Package Width                | 3.5 in [90 mm]   |
| Package Height               | 1.2 in [31 mm]   |
| Shipping (Package)<br>Weight | 1.8 oz [50 g]    |

---

**What's in the Box**

|                     |                  |
|---------------------|------------------|
| Included in Package | SFP+ Transceiver |
|---------------------|------------------|

---

***\*Product appearance and specifications are subject to change without notice.***

