

Product data sheet

Characteristics

NSYAMPM1916TB

Mounting plate in galvanized steel, thickness 1.5 mm For boxes of H175W150 mm



Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Product or Component Type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	-
Mounting Location	Back studs
Mounting plate description	Plain
Range compatibility	Thalassa TBS Thalassa TBP
Device composition	1 mounting plate
Material	Galvanised steel

Complementary

Fixing mode	By screws M4 self tapping - on back studs
Height	Nominal 7.56 in (192 mm) Real 5.51 in (140 mm)
Width	Nominal 6.46 in (164 mm) Real 66.34 in (1685 mm)
Thickness	0.06 in (1.5 mm)
Net weight	0.22 lb(US) (0.1 kg)

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480166082
Nbr. of units in pkg.	1
Package weight(Lbs)	9.17 oz (260 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.08 in (0.2 cm)
Package 1 width	5.51 in (14 cm)
Package 1 Length	6.69 in (17 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------
